

P.282

型式		NT\$ 單價			
Type	D	1~99 pcs	100~499	500~1999	2000~4000
MSTP	5	33	21	19	18
	6	21	14	13	12
		24	15	14	14
	8	21	14	13	12
		27	17	16	15
	10	54	34	32	31
		24	15	14	14
		30	19	18	17
		54	34	32	31
	12	38	24	23	22
		54	34	32	31
	13	38	24	23	22
		44	27	26	24
		54	34	32	31
	16	54	34	32	31

訂正用

1~99 pcs	100~499
33	21
21	14
24	15
21	14
27	17
54	34
24	15
30	19
54	34
38	24
54	34
38	24
44	27
54	34
54	34

型式		NT\$ 單價				MST
Type	D	1~99 pcs	100~499	500~1999	2000~4000	
MST (p6型)	5	33	21	19	18	
	6	21	14	13	12	
		24	15	14	14	
	8	21	14	13	12	
		27	17	16	15	
	10	54	34	32	31	
		24	15	14	14	
		30	19	18	17	
		54	34	32	31	
	12	38	24	23	22	
		54	34	32	31	
	13	38	24	23	22	
		44	27	26	24	
		54	34	32	31	
	16	48	31	29	28	
		54	34	32	31	
20	75	48	45	43		

1~99 pcs	100~499
33	21
21	14
24	15
21	14
27	17
54	34
24	15
30	19
54	34
38	24
54	34
38	24
44	27
54	34
48	31
54	34
75	48

型式		NT\$ 單價				MSTM
Type	D	1~99 pcs	100~499	500~1999	2000~4000	
MSTM (p6型)	5	33	21	19	18	
	6	21	14	13	12	
		24	15	14	14	
	8	21	14	13	12	
		27	17	16	15	
	10	54	34	32	31	
		24	15	14	14	
		30	19	18	17	
		54	34	32	31	
	12	38	24	23	22	
		54	34	32	31	
	13	38	24	23	22	
		44	27	26	24	
		54	34	32	31	
	16	48	31	29	28	
		54	34	32	31	
20	75	48	45	43		

1~99 pcs	100~499
33	21
21	14
24	15
21	14
27	17
54	34
24	15
30	19
54	34
38	24
54	34
38	24
44	27
54	34
48	31
54	34
75	48