







無錐度成形銷

Type	Group	Head Thickness	Tolerance			Material				Page
			Shaft Diameter	Tip Part	Length	SKH51 Equivalent	SKD61 Equivalent	NAK80	SUS440C	
軸徑固定 	Standard	4mm (T4)	0/-0.005	0/-0.01	+0.02/0	CPHS-□□	CPPS-□□	CPKS-□□	CPWS-□□	579
	Precision		0/-0.005	0/-0.005	+0.01/0	CPVS-□□	CPZS-□□	-	-	575
	Extra Precision		0/-0.003	0/-0.003	+0.01/0	CPMS-□□	-	-	-	571
軸徑指定 	Standard	4mm (T4)	0/-0.005	0/-0.01	+0.02/0	CPHBS-□□	CPPBS-□□	CPKBS-□□	CPWBS-□□	581
	Precision		0/-0.005	0/-0.005	+0.01/0	CPVBS-□□	CPZBS-□□	-	-	577
	Extra Precision		0/-0.003	0/-0.003	+0.01/0	CPMBS-□□	-	-	-	509
軸徑固定 -拋光處理-	Standard	4mm (T4)	0/-0.005	0/-0.01	+0.02/0	L-CPHS-□□	L-CPPS-□□	-	-	-
軸徑指定 -拋光處理-	Standard	4mm (T4)	0/-0.005	0/-0.01	+0.02/0	L-CPHBS-□□	L-CPPBS-□□	-	-	-
附逃氣孔 軸徑指定 	Standard	4mm (T4)	0/-0.005	0/-0.01	+0.02/0	GV-CPHS-□□	GV-CPPS-□□	-	-	585
	Precision		0/-0.005	0/-0.005	+0.01/0	GV-CPVS-□□	GV-CPZS-□□	-	-	585
附逃氣孔 軸徑指定 	Standard	4mm (T4)	0/-0.005	0/-0.01	+0.02/0	GV-CPHBS-□□	GV-CPPBS-□□	-	-	587
	Precision		0/-0.005	0/-0.005	+0.01/0	GV-CPVBS-□□	GV-CPZBS-□□	-	-	587
無錐度二段成形銷 軸徑固定 	Precision	4mm (T4)	0/-0.005	0/-0.005	+0.01/0	C□SV□□	C□SZ□□	-	-	591
無錐度二段成形銷 軸徑指定 	Precision		0/-0.005	0/-0.005	+0.01/0	C□SVB□□	C□SZB□□	-	-	593

※公差範圍代表值,依據全長而公差範圍會1mm~10mm