

灌嘴

Ecology Sprue Bushings							
Category	Type		S45C	HPM Equivalent	SKD61	DC53	Page
汎用螺栓型 T=10mm		Straight	-	SBBPE	SBBKE	-	-
		Tapered	-	SBGPE	SBGKE	-	
肩部型		Straight	-	SBSME	SBSDE	-	-
		Tapered	-	SBTME	SBTDE	-	
汎用螺栓型 T=10mm (舊JIS A型)		Straight	SJACE	SJAME	SJADE	-	-
		Tapered	SJGCE	SJGME	SJGDE	-	
専用螺栓型 T=10mm		Straight	-	SBBME	SBBDE	-	-
		Tapered	-	SBGME	SBGDE	-	

Bolt type											
Category	Type		S45C		HPM Equivalent		SKD61		DC53		Page
			Normal	String Eliminator	Normal	String Eliminator	Normal	String Eliminator	Normal	String Eliminator	
汎用螺栓型 T=10mm/P3.5/SR11		Straight	-	-	SBBP-B	SBBPH-B	SBBK-B	SBBKH-B	SBBS-B	SBBSH-B	851
汎用螺栓型 T=10mm		Straight	-	-	SBBP	SBBPH	SBBK	SBBKH	SBBS	SBBSH	853
		Tapered	-	-	SBGP	SBGPH	SBGK	SBGKH	SBGS	SBGSH	
汎用螺栓型 T=10mm 板厚選擇		Straight	-	-	-	SBBJH	-	SBBYH	-	-	843
汎用螺栓型 T=10mm (舊JIS A型)		Straight	SJAC	SJACH	SJAM	SJAMH	SJAD	SJADH	-	-	859
		Tapered	SJGC	SJGCH	SJGM	SJGMH	SJGD	SJGDH	-	-	
汎用螺栓型 T=10mm		Straight	-	-	SBBM	SBBMH	SBBD	SBBDH	-	-	861
		Tapered	-	-	SBGM	SBGMH	SBGD	SBGDH	-	-	
汎用螺栓型 T=15mm		Straight	-	-	SBBH	SBBHH	SBBT	SBBTH	SBBX	SBBXH	855
		Tapered	-	-	SBGH	SBGHH	SBGT	SBGTH	SBGX	SBGXH	
汎用螺栓型 T=20mm		Straight	SBBG	SBBFH	SBBR	SBBRH	-	-	-	-	857
		Tapered	SBGF	SBGFH	SBGR	SBGRH	-	-	-	-	
汎用螺栓型 T=8mm		Straight	-	-	SBBZSBBZS	-	SBBVSBBVS	-	-	-	-
		Tapered	-	-	BBZTSBBZT	-	BBVTSBBVT	-	-	-	

Shoulder Type											
Category	Type		S45C		HPM Equivalent		SKD61		DC53		Page
			Normal	String Eliminator	Normal	String Eliminator	Normal	String Eliminator	Normal	String Eliminator	
肩部型		Straight	-	-	SBSM	SBSMH	SBSD	SBSDH	SBSS	SBSSH	863
		Tapered	-	-	SBTM	SBTMH	SBTD	SBTDH	SBTS	SBTSH	
舊JIS B 型		Straight	SJBC	SJBCH	SJBM	SJBMH	SJBD	SJBDH	-	-	865
		Tapered	SJTC	SJTCH	SJTM	SJTMH	SJTD	SJTDH	-	-	

Extension nozzle type							
Category	Type		S45C	HPM Equivalent	SKD61	DC53	Page
N 部尺寸指定		Tapered	-	SXWM	-	-	847
噴嘴壺合型		Tapered	-	SXHM	SXHD	-	-
小徑灌嘴型		Straight	-	SXM	SXD	-	881
		Tapered	-	SXTM	SXTD	-	
大徑灌嘴型		Straight	-	SXDM	SXDD	-	
		Tapered	-	SXGM	SXGD	-	
特殊灌嘴型		Straight	-	SXCM	SXCD	-	
		Tapered	-	SXSM	SXSD	-	