

▼ 對應基恩斯KV-7000系列電纜線 腳針分配圖

KV-SIR32XT			
GP□-K62Y/GP□-K62T		GP□-K63Y/GP□-K63T	
左側 (CN1)		右側 (CN2)	
訊號名	腳針	訊號名	腳針
000	1 2	200	1 2
001	3 4	201	3 4
002	5 6	202	5 6
003	7 8	203	7 8
004	9 10	204	9 10
005	11 12	205	11 12
006	13 14	206	13 14
007	15 16	207	15 16
008	17 18	208	17 18
009	19 20	209	19 20
010	21 22	210	21 22
011	23 24	211	23 24
012	25 26	212	25 26
013	27 28	213	27 28
014	29 30	214	29 30
015	31 32	215	31 32
COM0	33 34	COM1	33 34
COM0	35 36	COM2	35 36
	37 38	COM2	37 38
	39 40	COM3	39 40

MIL插座公端40芯 MIL插座公端40芯

KV-SH04PL			
GP□-K64Y/GP□-K64T		GP□-K65Y/GP□-K65T	
軸1-軸2連結器		軸3-軸4連結器	
訊號名	腳針	訊號名	腳針
1LSF	1 2	2LSF	1 2
1LSR	3 4	2LSR	3 4
1ORG	5 6	2ORG	5 6
1STOP	7 8	2STOP	7 8
1SPOST	9 10	2SPOST	9 10
1Z+	11 12	2Z+	11 12
1Z-	13 14	2Z-	13 14
1SVEND	15 16	2SVEND	15 16
1SVRDY	17 18	2SVRDY	17 18
1ALM	19 20	2ALM	19 20
1ALMRES	21 22	2ALMRES	21 22
1SVON	23 24	2SVON	23 24
1CLR	25 26	2CLR	25 26
1FP+	27 28	2FP+	27 28
1FP-	29 30	2FP-	29 30
1RP+	31 32	2RP+	31 32
1RP-	33 34	2RP-	33 34
	35 36		35 36
+5V_OUT	37 38	-COM	37 38
+COM	39 40	-COM	39 40

MIL插座公端40芯 MIL插座公端40芯

KV-SSC02			
GP□-K66Y/GP□-K66T		輸入輸出連結器	
訊號名	腳針	訊號名	腳針
CH0_A+24V	1 2	CH1_A+24V	1 2
CH0_A+12V	3 4	CH1_A+12V	3 4
CH0_A+5V	5 6	CH1_A+5V	5 6
CH0_A-COM	7 8	CH1_A-COM	7 8
CH0_B+24V	9 10	CH1_B+24V	9 10
CH0_B+12V	11 12	CH1_B+12V	11 12
CH0_B+5V	13 14	CH1_B+5V	13 14
CH0_B-COM	15 16	CH1_B-COM	15 16
CH0_Z+24V	17 18	CH1_Z+24V	17 18
CH0_Z+12V	19 20	CH1_Z+12V	19 20
CH0_Z+5V	21 22	CH1_Z+5V	21 22
CH0_Z-COM	23 24	CH1_Z-COM	23 24
CH0_IN-CPT0	25 26	CH1_IN-CPT0	25 26
CH0_IN-CPT1	27 28	CH1_IN-CPT1	27 28
CH0_OUT0	29 30	CH1_OUT0	29 30
CH0_OUT1	31 32	CH1_OUT1	31 32
DATA+	33 34	DATA-	33 34
CLK+	35 36	CLK-	35 36
+5V	37 38	SG	37 38
COM-IN	39 40	COM-OUT	39 40

MIL插座公端40芯

* 為區分訊號名,訊號名與PLC製造商手冊中的訊號名有所差異,請務必確認后購買。
無訊號名的腳針無法連接。本公司根據電纜線所需腳針數對電纜線進行選定。

