

CAD資料夾名稱: 52\_Sanitary\_Vacuum\_Tanks

**雙銲接L形**

Type	材質
SNWE	SUS304
SNWES	SUS316L

RoHS

---

**雙銲接45°L形**

Type	材質
SNWHE	SUS304
SNWHES	SUS316L

RoHS

---

**雙銲接T形**

Type	材質
SNWT	SUS304
SNWTS	SUS316L

RoHS

---

**雙銲接異徑T形**

Type	材質
SNWTD	SUS304

RoHS

---

**隱藏式螺帽**

Type	材質
SNYBN	SUS304

RoHS

型式	Type	No.	D	d	L	SNWE		SNWES	
						NTS標準單價	NTS折扣單價	NTS標準單價	NTS折扣單價
SNWES	8A	13.8	10.5	38	—	—	—	—	
	10A	17.3	14.0		—	—	—	—	
	15A	21.7	17.5		—	—	—	—	
SNWE SNWES	1S	25.4	23	34	—	—	—	—	
	1.5S	38.1	35.7	49	—	—	—	—	
	2S	50.8	47.8	61	—	—	—	—	
	2.5S	63.5	59.5	84	—	—	—	—	
	3S	76.3	72.3	89	—	—	—	—	

超過表中最大數量時請至WOS確認。

型式	Type	No.	D	d	L	SNWHE		SNWHES	
						NTS標準單價	NTS折扣單價	NTS標準單價	NTS折扣單價
SNWHE SNWHES	1S	25.4	23	15.8	—	—	—	—	
	1.5S	38.1	35.7	23.7	—	—	—	—	
	2S	50.8	47.8	31.6	—	—	—	—	
	2.5S	63.5	59.5	42	—	—	—	—	
	3S	76.3	72.3	52.6	—	—	—	—	

超過表中最大數量時請至WOS確認。

型式	Type	No.	D	d	L	SNWT		SNWTS	
						NTS標準單價	NTS折扣單價	NTS標準單價	NTS折扣單價
SNWT SNWTS	1S	25.4	23.0	34.0	—	—	—	—	
	1.5S	38.1	35.7	49.0	—	—	—	—	
	2S	50.8	47.8	61.0	—	—	—	—	
	2.5S	63.5	59.5	84.0	—	—	—	—	
3S	76.3	72.3	89.0	—	—	—	—		

超過表中最大數量時請至WOS確認。

型式	Type	No.	D1	d1	D2	d2	L1	L2	NTS標準單價
									1~10 pcs
SNWTD	1.5S-1S	38.1	35.7	25.4	23.0	49	45	—	
	2S-1S	50.8	47.8	25.4	23.0	61	51	—	
	2S-1.5S	50.8	47.8	38.1	35.7	61	64	—	
	2.5S-1.5S	63.5	59.5	38.1	35.7	84	70	—	
	2.5S-2S	63.5	59.5	50.8	47.8	84	82	—	

超過表中最大數量時請至WOS確認。

型式	Type	No.	A	B	(T)	NTS標準單價	NTS折扣單價
						1~4 pcs	5~10
SNYBN	1S	46.0	53.1	30.0	—	—	
	1.5S	56.0	64.6		—	—	
	2S	71.0	81.9		—	—	
	2.5S	85.0	98.1		—	—	
	3S	100.0	115.4		—	—	

超過表中最大數量時請至WOS確認。

CAD資料夾名稱: 52\_Sanitary\_Vacuum\_Tanks

**銲接螺牙座**

Type	材質
SNYNS	SUS304

RoHS

---

**銲接襯套**

Type	材質
SNYRN	SUS304

RoHS

---

**六角螺帽**

Type	材質
SNRN	SUS304

RoHS

---

**L型墊圈**

Type	材質
SNLGS	矽膠
SNLGSF	PTFE

RoHS

---

**外螺牙型**

Type	材質
SNWZFA	SUS316L

RoHS

---

**軟管型**

Type	材質
SNWHAD	SUS304

RoHS

型式	Type	No.	D	d	NTS標準單價	NTS折扣單價
					1~9 pcs	10~20
SNYNS	1S	25.4	23.0	—	—	
	1.5S	38.1	35.7	—	—	
	2S	50.8	47.8	—	—	
	2.5S	63.5	59.5	—	—	
	3S	76.3	72.3	—	—	

超過表中最大數量時請至WOS確認。

型式	Type	No.	D	d	NTS標準單價	NTS折扣單價
					1~9 pcs	10~20
SNYRN	1S	25.4	23.0	—	—	
	1.5S	38.1	35.7	—	—	
	2S	50.8	47.8	—	—	
	2.5S	63.5	59.5	—	—	
3S	76.3	72.3	—	—		

超過表中最大數量時請至WOS確認。

型式	Type	No.	A	(B)	NTS標準單價	NTS折扣單價
					1~9 pcs	10~20 pcs
SNRN	1S	46	53.1	—	—	
	1.5S	56	64.6	—	—	
	2S	71	81.9	—	—	
	2.5S	85	98.1	—	—	
3S	100	115.4	—	—		

超過表中最大數量時請至WOS確認。

型式	Type	No.	A		SNLGS		SNLGSF	
			NTS標準單價	NTS折扣單價	NTS標準單價	NTS折扣單價		
SNLGS SNLGSF	1S	32.5	33.4	—	—	—	—	
	1.5S	46.0	46.8	—	—	—	—	
	2S	59.5	60.5	—	—	—	—	
	2.5S	73.2	74.0	—	—	—	—	
	3S	86.5	87.0	—	—	—	—	

請配合銲接螺牙座(SNYNS)使用。 超過表中最大數量時請至WOS確認。

Order 訂購範例: SNYNS1S

Delivery 出貨日: WOS

Price 價格: WOS

Example 使用範例: 銲接螺牙座, 銲接襯套, 六角螺帽, L型墊圈

型式	Type	No.	No.	R (PT)	A	B	C	D	L1	L2	NTS標準單價	NTS折扣單價
											1~4 pcs	5~10
SNWZFA	1S	4	1/2	21.7	15.7	25.4	23	39	7	—	—	
		6	3/4	27.2	21	25.4	23	39	7	—	—	
		8	1	34	26	25.4	23	39	7	—	—	
	1.5S	8	1	34	26	38.1	35.7	39	7	—	—	
		10	1 1/4	42.7	35.7	38.1	35.7	44	7	—	—	
		12	1 1/2	48.6	40	50.8	47.8	49	—	—	—	

超過表中最大數量時請至WOS確認。

型式	Type	No.	D	L	NTS標準單價	NTS折扣單價
					1~9 pcs	10~14
SNWHAD	1S	25.4	60	—	—	
	1.5S	38.1	80	—	—	
	2S	50.8	80	—	—	
	2.5S	63.5	80	—	—	
3S	76.3	80	—	—		

超過表中最大數量時請至WOS確認。

Order 訂購範例: SNWE2S

Delivery 出貨日: WOS

Price 價格: WOS

Example 使用範例: 銲接螺牙座, 銲接襯套, 六角螺帽, L型墊圈

Order 訂購範例: SNWTD2S-1.5S, SNWZFA1S

Delivery 出貨日: WOS

Price 價格: WOS