

內六角孔螺絲

—三價鉻酸鹽—

CAD資料夾名稱: 34_Screws

CBE

☑ 材質 SCM435
☑ 表面處理 三價鉻酸鹽
☑ 硬度 HRC32~39
※強度區分 10.9

M×P	A	E	B
2×0.4	3.8	2	1.5
2.6×0.45	4.5	2.6	2
3×0.5	5.5	3	2.5
4×0.7	7	4	3
5×0.8	8.5	5	4
6×1.0	10	6	5
8×1.25	13	8	6
10×1.5	16	10	8
12×1.75	18	12	10

※強度區分是指螺牙的拉伸強度。
(例) 10.9
表示降伏點或耐力的最小值為拉伸強度的90%。
表示拉伸強度的最小值為1040N/mm²。

參考: 內六角孔螺絲之沉頭及螺絲孔的尺寸 P.1909

型式	ℓ	NTS標準單價				NTS折扣單價			
		1~9 pcs	10~19 pcs	20~49 pcs	50~500 pcs				
Type M-L									
CBE 2-5									
6	全螺牙								
8									
10									
CBE 2.6-5									
6	全螺牙								
8									
10									
CBE 3-4									
5									
6									
8	全螺牙								
10									
12									
15									
18									
20									
25									
30	18								
35									
CBE 4-5									
6									
8									
10	全螺牙								
12									
15									
18									
20									
25									
30									
35									
CBE 5-6									
8	全螺牙								
10									
12									

型式	ℓ	NTS標準單價				NTS折扣單價			
		1~9 pcs	10~19 pcs	20~49 pcs	50~500 pcs				
Type M-L									
CBE 5-15									
18	全螺牙								
20									
25									
30									
35									
40	22								
45									
50									
CBE 6-8									
10									
12	全螺牙								
15									
18									
20									
25									
30									
35									
40									
45									
50									
55									
60									
CBE 8-10									
12									
15									
18	全螺牙								
20									
25									
30									
35									
40									
45									
50									
55									
60									

型式	ℓ	NTS標準單價				NTS折扣單價			
		1~9 pcs	10~19 pcs	20~49 pcs	50~300 pcs				
Type M-L									
CBE 8-60									
65									
70	28								
75									
80									
CBE 10-15									
20									
25	全螺牙								
30									
35									
40									
45									
50									
55									
60	32								
65									
70									
75									
CBE 12-15									
20									
25									
30	全螺牙								
35									
40									
45									
50									
55									
60									

Order 訂購範例

型式 CBE4-10

Delivery 出貨日

Price 價格

WEB WOS

內六角孔螺絲/內六角孔螺絲

—三價鉻酸鹽·袋裝販售— 鍍白鋅—

CAD資料夾名稱: 34_Screws

PACK-SCBE

☑ 材質 SCM435
☑ 表面處理 三價鉻酸鹽
☑ 硬度 HRC32~39
※強度區分 10.9

CBM

☑ 材質 SCM435
☑ 表面處理 鍍白鋅
☑ 硬度 HRC32~39
※強度區分 10.9

☑ CBM為RoHS非對應商品

型式	ℓ	PACK-SCBE		PACK-SCBE	
		每袋數量	NTS標準單價	NTS折扣單價	NTS標準單價
Type M-L					
PACK-2-5 SCBE		1~4袋			
6	全螺牙				
8					
10					
PACK-2.6-5 SCBE					
6	全螺牙				
8					
10					
PACK-SCBE					
35					
6					
8	全螺牙				
10					
12					
15					
20					
25					
30					
35					
40					
45					
50					
60					
PACK-4-6 SCBE					
8					
10	全螺牙				
12					
15					
20					
25					
30					
35					
40					
45					
50					
55					
60					
PACK-5-8 SCBE					
10	全螺牙				
12					
15					
20					
25					
30					
35					
40					
45					
50					
55					
60					

型式	ℓ	PACK-SCBE		PACK-SCBE	
		每袋數量	NTS標準單價	NTS折扣單價	NTS標準單價
Type M-L					
PACK-6-8 SCBE					
10	全螺牙				
12					
15					
20					
25					
30					
35					
40					
45					
50					
60					
PACK-8-12 SCBE					
15	全螺牙				
20					
25					
30					
35					
40					
45					
50					
55					
60					
PACK-10-15 SCBE					
20	全螺牙				
25					
30					
35					
40					
45					
50					
55					
60					
PACK-12-15 SCBE					
20	全螺牙				
25					
30					
35					
40					
45					
50					
55					
60					

*ℓ部是以JIS B 1176(2000)為基準。

Order 訂購範例

型式 PACK-SCBE6-10 CBM8-20

Delivery 出貨日

Price 價格

WEB WOS

☑ PACK-SCBE為袋裝販售, CBM則為單品販售。
☑ 袋裝販售品訂購數量1時為1袋。

型式	ℓ	NTS標準單價		NTS折扣單價	
		1~99 pcs	100~200 pcs	1~99 pcs	100~200 pcs
Type M-L					
CBM 3-6					
8	全螺牙				
10					
12					
15					
20					
25					
30					
35					
40					
45					
50					
55					
60					
CBM 4-6					
8					
10	全螺牙				
12					
15					
20					
25					
30					
35					
40					
45					
50					
55					
60					
CBM 5-8					
10	全螺牙				
12					
15					
20					
25					
30					
35					
40					
45					
50					
55					
60					
CBM 10-15					
20	全螺牙				
25					
30					
35					
40					
45					
50					
55					
60					
CBM 12-15					
20	全螺牙				
25					
30					
35					
40					
45					
50					
55					
60					