

新商品

FITTING FOR HIGH PRESSURE

高壓用接頭

—異徑型—

CAD資料夾名稱: Joints

鋼管用接頭



Table with columns: Type, 材質. Rows: SGPSDJ (S25C), SUTSSJ (SUS304). Includes a technical drawing of the fitting with dimensions T1, T2, L, and Ø.

鋼管用接頭



Table with columns: Type, 材質. Rows: SGPNPJ (S25C), STUPDJ (SUS316). Includes a technical drawing of the fitting with dimensions B, L, (ℓ1), A, (ℓ2), T1, and T2.

鋼管用接頭



Table with columns: Type, 材質. Rows: SGPTDJ (S25C), SUTPDJ (SUS304). Includes a technical drawing of the fitting with dimensions (B), T1, T2, and (A).

鋼管用接頭



Table with columns: Type, 材質. Rows: SGPPBJ (S25C), SUTPBJ (SUS304). Includes a technical drawing of the fitting with dimensions (B), L, C, (ℓ), T1, and T2.

規格

Table with columns: 接頭材質, 最高使用溫度, 最高使用壓力, 適用配管. Rows: S25C, SUS304.

\* S25C材質依JIS B2316(2欄)規格製作、SUS304材質依JIS B2316(1欄)規格製作。

Table with columns: 型式, Rc(PT), SGPSDJ, SUTSSJ, NTS單價, SGPSDJ, NTS單價, SUTSSJ. Rows: 12, 23, 24, 34, 36, 46, 48, 68.

Table with columns: 型式, R(PT), SGPNPJ, STUPDJ, NTS單價, SGPNPJ, NTS單價, STUPDJ. Rows: 12, 23, 24, 34, 36, 46, 48, 68.

Table with columns: 型式, Rc(PT), SGPTDJ, SUTPDJ, NTS單價, SGPTDJ, NTS單價, SUTPDJ. Rows: 24, 34, 36, 46.

Table with columns: 型式, T1, T2, SGPPBJ, SUTPBJ, NTS單價, SGPPBJ, NTS單價, SUTPBJ. Rows: 12, 23, 24, 26, 34, 36, 38, 46, 48, 68.



4 日出貨 P.91

3日日出貨 僅限當日PM3:30前特別申請之訂單。

新商品

FITTING FOR HIGH PRESSURE

高壓用接頭

—焊接型—

CAD資料夾名稱: Joints

高壓焊接接頭



Table with columns: Type, 材質. Rows: SKPSH (S25C), SKTSH (SUS304). Includes a technical drawing of the fitting with dimensions C, E, C, D, A, and (B).

高壓焊接接頭



Table with columns: Type, 材質. Rows: SKPLH (S25C), SKTLH (SUS304). Includes a technical drawing of the fitting with dimensions E, C, D, A, and (B).

高壓焊接接頭



Table with columns: Type, 材質. Rows: SKPHEH (S25C), SKTHEH (SUS304). Includes a technical drawing of the fitting with dimensions E, C, D, A, and (B).

高壓焊接接頭



Table with columns: Type, 材質. Rows: SKPPTH (S25C), SKTPTH (SUS304). Includes a technical drawing of the fitting with dimensions E, C, D, A, and (B).

高壓焊接接頭



Table with columns: Type, 材質. Rows: SKPUH (S25C), SKTUH (SUS304). Includes a technical drawing of the fitting with dimensions L, M, O型環, C, A, D, and (H).

高壓焊接接頭



Table with columns: Type, 材質. Rows: SKPCH (S25C), SKTCH (SUS304). Includes a technical drawing of the fitting with dimensions K, C, A, and (B).

規格

Table with columns: 接頭材質, 最高使用溫度, 最高使用壓力, 適用配管. Rows: S25C, SUS304.

\* S25C材質依JIS B2316(2欄)規格製作、SUS304材質依JIS B2316(1欄)規格製作。

Table with columns: 型式, No., SKPSH, SKTSH, NTS單價, SKPSH, NTS單價, SKTSH. Rows: 6A, 8A, 10A, 15A, 20A, 25A, 32A, 40A, 50A.

Table with columns: 型式, No., SKPLH, SKTLH, NTS單價, SKPLH, NTS單價, SKTLH. Rows: 6A, 8A, 10A, 15A, 20A, 25A, 32A, 40A, 50A.

Table with columns: 型式, No., SKPHEH, SKTHEH, NTS單價, SKPHEH, NTS單價, SKTHEH. Rows: 6A, 8A, 10A, 15A, 20A, 25A, 32A, 40A, 50A.

Table with columns: 型式, No., SKPPTH, SKTPTH, NTS單價, SKPPTH, NTS單價, SKTPTH. Rows: 6A, 8A, 10A, 15A, 20A, 25A, 32A, 40A, 50A.

Table with columns: 型式, No., SKPUH, SKTUH, NTS單價, SKPUH, NTS單價, SKTUH. Rows: 8A, 10A, 15A, 20A, 25A, 32A, 40A, 50A.

Table with columns: 型式, No., SKPCH, SKTCH, NTS單價, SKPCH, NTS單價, SKTCH. Rows: 6A, 8A, 10A, 15A, 20A, 25A, 32A, 40A, 50A.



4 日出貨 P.91

3日日出貨 僅限當日PM3:30前特別申請之訂單。

鋼管、軟管 配管相關零件