





單階成形銷

Straight Core Pins												
Type	Material											Page
	SKH51 Equivalent	SKD61 Equivalent	NAK80	DH2F	STAVAX Prehardened	STAVAX Hardened	PROVA400 Prehardened	PROVA400 Hardened	SUS440C	C1720 Beryllium copper	MAS1C	
L 全長指定 	CPM-L	-	-	-	-	-	-	-	-	-	-	453
	CPV-L	CPZ-L	-	-	-	-	-	-	-	-	-	453
	CPH-L	CPP-L	CPK-L	CPG-L	CPE-L	CPEH-L	CPR-L	CPRH-L	CPW-L	CPC-L	CPY-L	453 459
	CPX-L	CPD-L	CPN-L	CPF-L	CPT-L	CPTH-L	CPQ-L	CPQH-L	-	-	CPA-L	
	-	CPDJ-L	-	-	-	-	-	-	-	-	-	-
L・P 軸徑・全長指定 	CPMB-L	-	-	-	-	-	-	-	-	-	-	455
	CPVB-L	CPZB-L	-	-	-	-	-	-	-	-	-	455
	CPHB-L	CPPB-L	CPKB-L	CPGB-L	CPEB-L	CPEHB-L	CPRB-L	CPRHB-L	CPWB-L	CPCB-L	CPYB-L	455 459
	CPXB-L	CPDB-L	CPNB-L	CPFB-L	CPTB-L	CPTHB-L	CPQB-L	CPQHB-L	-	-	-	
	-	CPDJB-L	-	-	-	-	-	-	-	-	-	-
P 軸徑指定 L 全長固定 	CPH-G	CPP-G	-	-	-	-	-	-	-	-	-	457
	CPX-G	CPD-G	-	-	-	-	-	-	-	-	-	457
前端加工・ L 全長指定 	CPML□	-	-	-	-	-	-	-	-	-	-	469
	CPVL□	CPZL□	-	-	-	-	-	-	-	-	-	473
	CPHL□	CPPL□	CPKL□	CPGL□	-	-	-	-	CPWL□	CPCL□	CPYL□	479
	CPXL□	CPDL□	CPNL□	CPFL□	-	-	-	-	-	-	CPAL□	479
	-	CPDJL□	-	-	-	-	-	-	-	-	-	-
前端加工・軸徑・ L 全長指定 	CPMBL□	-	-	-	-	-	-	-	-	-	-	471
	CPVBL□	CPZBL□	-	-	-	-	-	-	-	-	-	475
	CPHBL□	CPDBL□	CPKBL□	CPGBL□	-	-	-	-	CPWBL□	CPCBL□	CPYBL□	481
	CPXBL□	CPDBL□	CPNBL□	CPFBL□	-	-	-	-	-	-	CPABL□	481
	-	CPDJBL□	-	-	-	-	-	-	-	-	-	-
自由指定型 	F-CPH□	F-CPD□	F-CPN□	F-CPF□	-	-	-	-	-	F-CPC□	-	485
	F-CPHE□	F-CPDE□	F-CPNE□	F-CPFE□	-	-	-	-	-	F-CPCE□	-	485
前端加工・ L 全長指定 	CPH□□ CPHB□□	CPP□□ CPPB□□	-	-	-	-	-	-	-	-	-	-
	CPX□□ CPXB□□	CPD□□ CPDB□□	-	-	-	-	-	-	-	-	-	-
成形銷半成品 	CPH	-	-	-	-	-	-	-	-	-	-	491
	-	CPD	-	-	-	-	-	-	-	-	-	491

※ 公差範圍代表值,依據全長而公差範圍會1mm~10mm

GAS RELEASE STRAIGHT CORE PINS

[illegible]

STRAIGHT CORE PINS With Engraving

[illegible]