■頭部R型

STOPPER BOLTS STOPPER SCREWS 止動螺栓/止動螺絲

● CAD資料夾名稱: 23_Locating_&_Guide_Components

■螺帽T尺寸

M T T1


●超過表由是大數是時誌至WAS確認



頭部R型	內六角孔頭部R型	附屬螺帽 (30°)	М	M×Pitch 細螺紋 粗螺紋	SR ₂ ((l)	1) (l2)	В1	B (C)
\$ <u>™</u> \$	SR ₂		4	4×0.5 4×0.7 2.8	- X II	2.	1 2.2	2	7 8.1
SR ₂			_ 5	5×0.5 5×0.8 3.5			4 2.8	2.5	8 9.2
 	 	() () () () () () () () () ()	_6	6×0.75 6×1.0 4	10 0	0.3 3.0	0 3	3 1	0 11.5
6.3// (ℓ1)	6.3		8_	8×0.758×1.25 5.5	12 ().4 3.7	7 4	4 1	3 15.0
前端部淬火/上	前端部淬火 (ℓ1) (ℓ2)	_B1_ B T (T) 10	10×1.010×1.5 7	16).5	5 5	5 1	7 19.6
* SUS304無淬火	H L	В	12	12×1.0 12×1./5 8	20	5.2	2 6	6	9 21.9
			16	16×1.5[16×2.0] TU	25	J.6 6		- 2	24 27.7

	■與部K型							
ĺ	型式		L選擇		CB · STBB	STCBM · STBBM	STBBS	SSTCB · SSTBB
Ī	Turno	м	STCB · STBB STCBM · SSTCB · STBBM	NT\$基準單價	NT\$折扣單價	NT\$基準單價 NT\$折扣單價	NTS基準單價 NTS折扣單價	NTS基準單價 NTS折扣單價
	Type	IVI	STBBS · SSTBB	1~3 pcs	4~49 pcs 50~100 pcs	1~49 pcs 50~100 pcs	1~49 pcs 50~100 pcs	1~49 pcs 50~100 pcs
	(細螺紋)	4	10 15 20 25 30 35 40					
	STCB	5	10 15 20 25 30 35 40 50					
	STCB STCBM SSTCB	6	15 20 25 30 35 40 50 20 25 30 40 50					
	(粗螺紋) STBB STBBM STBBS SSTBB	8	15 20 25 30 35 40 50 60 70 80 25 30 40 50 60					
	STBB	10	30 35 40 50 60 70 80 30 40 50 60 70					
	STERS	12	30 35 40 50 60 70 80 40 50 60 70 80					
	SSTBB	16	50 60 70 80 —			_	_	_


■內六角孔頭部	『R型												•	但应 於「一般八數里	NY RH IL WOODE DES
型式											BC		·STBCM		· SSTBC
Type	М				Li	選擇				NT\$基準單價	NT\$折扣單價	NT\$基準單價			NT\$折扣單價
Type	IVI									1~49 pcs	50~100 pcs	1~49 pcs	50~100 pcs	1~49 pcs	50~100 pcs
(細螺紋)	4	20													
STCCM	5	20													
SSTCC (粗螺紋)	6	20	25	30	40	50									
STBC	8		25	30	40	50	60								
STBCM	10			30	40	50	60	70							
SSTBC	12				40	50	60	70	80						



型式			L選擇																STCA · STBA			STCAM · STBAM		STBAS		SSTCA		
Type	м			5	STO	CA	· S1	ГВА				ST							٩M	NTS基準單價				NTS折扣單價				
													<u> </u>) I B	<u>AS</u>	• SS	IR	<u> </u>		1~3 pcs	4~49 pcs	50~100 pcs	1~49 pcs	50~100 pcs	1~49 pcs	100 pcs	1~49 pcs	50~100 pcs
(細螺紋)	4	15 2	0 2	5 3	30	35	40					20																
SICA	5	15 2	0 2	5 3	30	35	40	50				20																
(細螺紋) STCA STCAM SSTCA	6	15 2	0 2	5 3	30	35	40	50				20	25	30	40	50												
(粗螺紋)	8	15 2	0 2	5 3	30	35	40	50	60	70	80		25	30	40	50	60											
STBA	10			- (30	35	40	50	60	70	80			30	40	50	60	70										
(粗螺紋) STBA STBAM STBAS SSTBA	12			- (30	35	40	50	60	70	80				40	50	60	70	80									
SSTBA	16							50	60	70	80				-	_							-	_	-	_	-	_

②超過表中最大數量時請至WOS確認。

■特長:因接觸面為平面,較不易磨損。




		型式			L	l l	7										NT\$基	準單價		
	Ту	ре		М	指定單位 5mm	粗螺紋	細螺紋	В	(C)	Н	(2)	(r)	ℓ1	B ₁	STRCB STRB	•	SSTRCB SSTRB		STRNCC STRNC	SSTRCC SSTRC
					10~30	3×0.5	-	5.5	6.4	2	1	0.1	_	_			_	_	_	_
一般型 內六角孔型			4	15~60	4×0.7	4×0.5	7	8.1	2.8	2.1	0.0	2.2	2							
((m)m(+)	(den (m (d))	(Am+m A+)	(de (m ())	5	15~60	5×0.8	5×0.5	8	9.2	3.5	2.4	0.2	2.8	2.5						
(細螺紋)	(粗螺紋)	(細螺紋)	(粗螺紋)	6	20~60	6×1.0	6×0.75	10	11.5	4	3	0.3	3	3						
STRCB STRCN	STRB STRN	STRCC	STRC STRNC	8	25~60	8×1.25	8×0.75	13	15.0	5.5	3.7	0.4	4	4						
SSTRCB	SSTRB	SSTRCC	SSTRC	10	30~70	10×1.5	10×1.0	17	19.6	7	4.5	0.5	5	5						
COMOD	COTTE	55.1100	551110	12	35~80	12×1.75	12×1.0	19	21.9	8	5.2	0.5	6	6						

▼*M3尺寸僅適用於STRB・STRN。










● CAD資料夾名稱: 23_Locating_&_Guide_Components

Alteration	Code	Spec.
L尺寸變更	LC	L尺寸以1mm為單位 做變更。 <u>指定方法</u> LC22 Lmin <lc<lmax 指定單位1mm</lc<lmax



型式					1 39	製選					M×Pitch 細螺紋	B ₁	0	(d)	NT\$基準單價			
Type	M		上送]辛									D1	, k	(u)	STSCC	STSNCC	SSTSCC	
	4	20 25	30	35	40						4×0.5	2	2.5	2.5				
STSCC	5	20 25	30	35	40						5×0.5	2.5	3	3.5				
STSNCC	6		30	35	40	45	50	60			6×0.75	3	3.5	4				
SSTSCC	8		30	35	40	45	50	60			8×0.75	4	5	4.5				
331300	10				40	45	50	60	70		10×1.0	5	6	7				
	12				40	45	50	60	70	80	12×1.0	6	8	8.5				







