附接頭板/簡易歧管





TERMINALS FOR PIPING 附接頭支撐座



●CAD資料夾名稱: 50_Manifolds








■凸字型	-																
型式	#II - Y						Α/		NT\$基準單價								
五式	H (接頭數)	Rc (PT)	_		W		В		TGMF		TGMS						
Type	No.	(]女刘安)		TGMF	TGMS	TGMF	TGMS		1H	2H	3H	1H	2H	3H			
TOME	1	1	1/8	25	25	34	35	28									
TGMF TGMS	2	2	1/4	29	29.5	38	39	32									
IGNIS	3	3	3/8	35	36	46.5	47.5	40									

■管接頭型	Į																			
刑士	型式		EE OF D				V			2	E		NT\$基準單價							
		(接頭數)	間距P 選擇	Rc(PT)		-	W		В					TGMSF		TGMSS				
Type	No.	(1女职安)	选择		TGMSF	TGMSS	TGMSF	TGMSS	TGMSF	TGMSS	TGMSF	TGMSS	1H	2H	3H	1H	2H	3H		
TGMSF	1	1	25	1/8	19	15	22	23	18	19	25	25								
	2	2	35 50	1/4	22	19	25	29	21	25	25	25								
TGMSS	3	3	50	3/8	28	22	28	30	24	26	30	25								
●□□□ 不示:	6十四 6日	9ED																		










■1段型																				
型式		管接頭數	V	В	Rc	В	6			W			TGL	B NT	\$基準	單價	TGLBS NT\$基準單價			
Type	No.	Н	T	ь	(PT)	T) F S TGLB TGLBS TGLBS TGLB TGLBS TGLBS TGLB TGLBS TGLBS TGLB TGLBS TGLBS								H4	H1	H2	H3	H4		
TOLD	1	1	40	30	1/8	30	20	19	15	22	23	SPCC								
TGLBS	2	3	50 60		1/4	40	25	22	19	25	29	2.3 SUS304D								
IGLBS	3	1	70	40	3/8	40	25	28	22	28	30	2.0								

■2段型																					
型式		管接頭數	V	В	Rc	В	P ₁	6	D		W			TGLBW NT\$基準單價				TGLBWS NT\$基準單價			
Type	No.	Н	T	В	(PT)	P	PI	3	TGLBW	TGLBWS	TGLBW	TGLBWS	١ ١	H2	H4	H6	H8	H2	H4	H6	H8
TCI DW	1	2	40	30	1/8	30	30	20	19	15	22	23	SPCC								
TOLDWO	2	6	50 60	40	1/4	40	40	25	22	19	25	29	2.3 SUS304D								
IGLBWS	3	8	70	50	3/8	40	40	25	28	22	28	30	2.0								



■1段型																				
型式		快速接頭數H	v	В	ь	•	_	w	螺牙尺寸	有效斷面積		NT\$基準單價								
Type	No.	大还按頭数口	ı		-	3	, ,	VV	M×間距	(mm²)		H1	H2	Н3	H4	H5	H6			
	4	1			28	14	14	32.6	M12×1	4.3	2.0									
	6	2	40 50 60 70	30	34	17	17		M14×1	12.7										
TGLCS	8	3			38	19	19		M16×1	23.4										
	10	5		40	48	24	24		M20×1	37.4										
	12	6			48	24	24		M22×1	53.6										

■2段型																				
型式		快速接頭數H	V	В	ь	D4		D	w	螺牙尺寸	有効斷面積	t	NT\$基準單價							
Type	No.	伏还按與数□	_ T	<u> </u>		FI	3	ט	VV	M×間距	(mm2)		H2	H4	H6	H8	H10	H12		
	4	2		30 40	28	28	14	14	33	M12×1	4.3	2.3								
	6	4	50 60 70		34	34	17	17	36	M14×1	12.7									
TGLCW	8	6			38	38	19	19	39	M16×1	23.4									
	10	10			48	48	24	23	44.5	M20×1	37.4									
	12	12			48	48	24	26	47	M22×1	53.6									





