




請依照選定步驟①~④選擇型式和數值後再行訂購。

Order 訂購範例	型式 (1) Type · 軟管No. (2) 軟管No. (標準) HOSVA2 (L型) HLVA2 (分岔型) HOSVAW2	軟管顏色 (3) 軟管顏色 B	鏈節數 (4) 鏈節數 n 20	連接器螺牙尺寸 (5) 連接器螺牙尺寸 2	鏈節數 (6) 鏈節數 m 5	鏈節數 (7) 鏈節數 m右 (R) R10	鏈節數 (8) 鏈節數 m左 (L) L7	噴嘴 (9) 噴嘴 D1
------------	--	-----------------	------------------	-----------------------	-----------------	------------------------	-----------------------	--------------



形狀A (A1 · A2 · A3)	形狀B (B1 · B2 · B3)	形狀C (C1 · C2)	形狀D (D1)	形狀M (M1 · M2)																																																											
<table border="1"> <tr><th>軟管No.</th><th>A1</th><th>A2</th><th>A3</th></tr> <tr><td>2</td><td>4.9</td><td>6.3</td><td>9.6</td></tr> <tr><td>3</td><td>9.5</td><td>13.0</td><td>15.0</td></tr> <tr><td>4</td><td>10.5</td><td>14.0</td><td>17.0</td></tr> </table>	軟管No.	A1	A2	A3	2	4.9	6.3	9.6	3	9.5	13.0	15.0	4	10.5	14.0	17.0	<table border="1"> <tr><th>軟管No.</th><th>B1</th><th>B2</th><th>B3</th></tr> <tr><td>2</td><td>4.1</td><td>5.6</td><td>9.0</td></tr> <tr><td>4</td><td>9.5</td><td>12.4</td><td>15.4</td></tr> </table>	軟管No.	B1	B2	B3	2	4.1	5.6	9.0	4	9.5	12.4	15.4	<table border="1"> <tr><th>軟管No.</th><th>C1</th><th>C2</th></tr> <tr><td>2</td><td>1.0</td><td>41.0</td></tr> <tr><td>4</td><td>1.5</td><td>41.0</td></tr> </table>	軟管No.	C1	C2	2	1.0	41.0	4	1.5	41.0	<table border="1"> <tr><th>軟管No.</th><th>d2</th><th>D1</th><th>d4</th></tr> <tr><td>2</td><td>1.7</td><td>26.8</td><td>34</td></tr> <tr><td>3</td><td>3</td><td>34</td><td>48</td></tr> <tr><td>4</td><td>4.5</td><td>48</td><td></td></tr> </table>	軟管No.	d2	D1	d4	2	1.7	26.8	34	3	3	34	48	4	4.5	48		<table border="1"> <tr><th>軟管No.</th><th>M1</th><th>M2</th></tr> <tr><td>2</td><td>Rc1/8</td><td>Rc1/4</td></tr> </table>	軟管No.	M1	M2	2	Rc1/8	Rc1/4
軟管No.	A1	A2	A3																																																												
2	4.9	6.3	9.6																																																												
3	9.5	13.0	15.0																																																												
4	10.5	14.0	17.0																																																												
軟管No.	B1	B2	B3																																																												
2	4.1	5.6	9.0																																																												
4	9.5	12.4	15.4																																																												
軟管No.	C1	C2																																																													
2	1.0	41.0																																																													
4	1.5	41.0																																																													
軟管No.	d2	D1	d4																																																												
2	1.7	26.8	34																																																												
3	3	34	48																																																												
4	4.5	48																																																													
軟管No.	M1	M2																																																													
2	Rc1/8	Rc1/4																																																													

標準型 軟管顏色: 指定 (藍色) · 噴嘴: 橘色 · 灰色 · 黑色

型式 (1) Type	軟管No. (2)	軟管顏色指定 (3)	鏈節數n指定 (4)	連接器螺牙尺寸 R/Rc (PT) (5)	選擇噴嘴 (9) (詳細尺寸請參照P.2818)
HOSAJ (外螺牙) HOSVA (外螺牙閥) *HOSVAF (內螺牙閥)	2 3 4	無指定 (藍色) G (灰色) B (黑色) 無指定 (藍色) G (灰色)	0~30	1 (R1/8) 2 (R1/4) 3 (R3/8) 4 (R1/2) 4 (R1/2)	2 (R/Rc1/4) 3 (R/Rc3/8) 4 (R/Rc1/2)

L型 軟管顏色: 藍色 噴嘴: 橘色

型式 (1) Type	軟管No. (2)	鏈節數n指定 (3)	連接器螺牙尺寸R(PT) (5)	鏈節數指定 m (6)	選擇噴嘴 (9) (詳細尺寸請參照P.2818)
HLAJ (外螺牙) HLVA (外螺牙閥)	2 4	0~30	1 (R1/8) 2 (R1/4) 3 (R3/8) 4 (R1/2)	0~20	A1 · A2 · A3 · B1 · B2 · B3 · C1 · C2 · D1 · M1 · M2 A1 · A2 · A3 · B1 · B2 · B3 · D1


分岔型 軟管顏色: 藍色 噴嘴: 橘色

型式 (1) Type	軟管No. (2)	鏈節數n指定 (3)	連接器螺牙尺寸R(PT) (5)	鏈節數指定 m (6)	選擇噴嘴 (9) (詳細尺寸請參照P.2818)
HOSAJW (外螺牙) HOSVAW (外螺牙閥)	2 4	0~30	1 (R1/8) 2 (R1/4) 3 (R3/8) 4 (R1/2)	0~20 0~20	A1 · A2 · A3 · B1 · B2 · B3 · C1 · C2 · D1 · M1 · M2 A1 · A2 · A3 · B1 · B2 · B3 · D1


Delivery 出貨日	5 日出貨	快件 第2日出貨	P.6	快件 第3日出貨	P.6
--------------	-------	----------	-----	----------	-----

請依照選定步驟①~④選擇型式和數值後再行訂購。

Order 訂購範例	型式 (1) Type · 軟管No. (2) 軟管No. HJD2	鏈節數 (3) 鏈節數 5	型式 (1) Type · 軟管No. (2) 軟管No. HAKD2	噴嘴 (9) 形狀 (3) 軟管No. (4) 軟管No. A1
	型式 (1) Type · 軟管No. (2) 軟管No. AAJD2	鏈節數 (3) 鏈節數 1	型式 (1) Type · 軟管No. (2) 軟管No. HOSAJT2	



型式 (1) Type	軟管No. (2)	鏈節數 (3)	軟管內徑 (4)	D	B	L1
HJD	2	5	6.6	15.9	14.5	20.0
	3		9.5	20.2	17.4	25.2
	4		12.6	25.2	21.0	29.9




型式 (1) Type	軟管No. (2)	連接器螺牙尺寸 R(PT) (3)	A	L	H	T
AAJD	2	1 (R1/8)	23	26.3	14	7
		2 (R1/4)				
	3	3 (R3/8)	27.3	32	19	8
		4 (R1/2)				
4	3 (R3/8)	28	38.3	18.8	7.5	
	4 (R1/2)					


型式 (1) Type	軟管No. (2)	連接器螺牙尺寸 R(PT) (3)	A	L	H	W
AVAD	2	2 (R1/4)	41	41	30	27
		3 (R3/8)	45	45	34	25
	4	4 (R1/2)	48.5	48.5	43	34

型式 (1) Type	軟管No. (2)	連接器螺牙尺寸 Rc (PT) (3)	A	L	H	W
AVAFD	2	2 (Rc1/4)	42	45	30	27
		4 (Rc1/2)	58.2	64	63	34

型式 (1) Type	軟管No. (2)	L2	L3	L4	L5
AAJL (L型) AAJY (Y型)	2	17	12	15.5	9.5
	4	23.5	16.5	23.5	19



型式 (1) Type	軟管No. (2)	噴嘴 (3) 形狀 (4) No.	A形狀	B形狀	C形狀	D形狀	M形狀	
HAKD	2	A B C D M	1	●	●	●	●	●
			2	●	●	●	●	●
			3	●	●	●	●	●
			4	●	●	●	●	●
			1	●	●	●	●	●
			2	●	●	●	●	●
	3	A B C D M	1	●	●	●	●	●
			2	●	●	●	●	●
			3	●	●	●	●	●
			4	●	●	●	●	●
			1	●	●	●	●	●
			2	●	●	●	●	●



型式 (1) Type	軟管No. (2)	加工適用表
HOSAJT	2	●
	3	●
	4	●