■吊環螺栓

31 螺螺帽絲

1939

LIFTING EYE BOLTS / SWING BOLTS 吊環螺栓/活節螺栓






LENGTH SPECIFIED SCREWS WITH HEXAGON SOCKETS / FULL THREAD 內六角全長指定螺絲/全螺牙型 -JIS2級-









型式		M×P	_	h	_	D	ш	0		_	R	do	螺帽		A Type	B Type
Type	M	IVI^P	а	р	·	D	п	Ł	е	g	n	da	В	T	N/1P{kgf/1P}	N/2P {kgf/2P}
	6	6×1.0	24.9	14.5	5.2	13	29	15	3	4.5	1	7.7	10	5	392 [40]	392 {40}
	8	8×1.25	32.6	20	6.3	16	33.3	15	3	6	1	9.2	13	6.5	785 {80}	785 {80}
CHIC	10	10×1.5	41	25	8	20	41.5	18	4	7.7	1.2	11.2	17	8	1471 {150}	1471 {150}
SCHI	12	12×1.75	50	30	10	25	51	22	5	9.4	1.4	14.2	19	10	2157 {220}	2157 {220}
	16	16×2.0	60	35	12.5	30	60	27	5	13	1.6	18.2	24	13	4413 {450}	4413 {450}
	20	20×2.5	72	40	16	35	71	30	6	16.4	2	22.4	30	16	6178 (630)	6178 (630)
	24	24×3.0	90	50	20	45	90	38	8	19.6	2.5	26.4	36	19	9316 (950)	9316 (950)



CAD 2D
























型式	,	3 L	D	В	84	F	
Type	⊘ P	5	D	Ь	М	r	
	6	30	12	6	6	22	
	0	50	12	O	O	30	
		30		8		20	
	8	50	16		8	30	
		60				30	
DNDN		50				30	
DIADIA	10	70	20	10	10	40	
		100				50	
	12	50				30	
		80	24	12	12	45	
		100				60	
	16	100	32	16	16	50	







交期另估