


精密固鎖螺帽/軸承螺帽用勾形扳手


● CAD資料夾名稱: 14_Bearings_with_Holder



型式		M×Pitch (細螺紋)	D	d	B	S	T	m	端面直角度 (Max)	最大緊固扭矩 (N・m) 固定螺絲	NTS基準單價	
Type	M										PLNY	PLN
(標準型) PLNY	8	8×0.75	16	11	8	3	2	2×M4	・ PLNY 0.005	3.5		
	10	10×1.0	18	13								
	12	12×1.0	20	16								
	15	15×1.0	25	21								
	17	17×1.0	28	23	10	4	2×M5 3×M5	・ PLNY 0.005	4.5			
	20	20×1.0	32	27								
	25	25×1.5	38	33	12	5	3×M6	・ PLN 0.002	8.0			
	30	30×1.5	45	40								
	35	35×1.5	52	47								
	40	40×1.5	58	52								
	45	45×1.5	65	59	14	6	2.5	3×M8	18.0			
	50	50×1.5	70	64								
55	55×2.0	75	68	16	7	3						
60	60×2.0	80	73									




■ 軸承螺帽用勾形扳手



型式		R1	R2	B	C	θ	T	H	L	適用外形	適用圓螺帽 軸承螺帽	NT\$基準單價 1~9pcs	NT\$折扣單價 10~50pcs	
Type	No.													
MFK	16	8	10	1.5	2	30°	4	11	108	φ16 × φ18	M8 × M10			
	20	10	11							φ20 × φ22	M12			
	25	12.5	14	2	2.3		35°	5	20	136	φ25 × φ28	M15 × M17		
	30	15	16								φ30 × φ32	M20		
	34	17	19					6	28	160	φ34 × φ38	M25		
	45	22.5	24	2.5	2.5	7		36	196	φ45 × φ48	M30			
	52	26	27.5			6.5		41	208	φ52 × φ55	M35			
	58	29	32.5	3.5	3	8.5	46	232	φ58 × φ65	M40 × M45				
	65	32.5	35						φ65 × φ70	M45 × M50				
	70	35	37.5				52	247	φ70 × φ75	M50 × M55				

⚠ 超過表中最大數量時交期另估




HARD LOCK NUTS FOR BEARING-SQUARE-HEXAGON TYPE-


防鬆脫軸承螺帽

—四角・六角型—

● CAD資料夾名稱：14_Bearings_with_Holder



型式		M×Pitch		D	d	F	B	C	S	m	粗螺紋NT\$基準單價			細螺紋NT\$基準單價		
Type	M	粗螺紋	細螺紋								BNG	BNGC	BNGC	BNR	BNRC	BNRS
BNG BNGC BNGC BNR BNRC BNRS	3	M3×0.5	M3×0.35	11.5	4	10	5.5	3	0.5	M3×3 (附套件)						
	4	M4×0.7	M4×0.5		5											
	5	M5×0.8	M5×0.5		9						11					
	6	M6×1.0	M6×0.75	14.5	10	12										
	8	M8×1.25	M8×1.0	17	13	14	6.5	4								
	10	M10×1.5	M10×1.0	20	16	17	8	5	1	M4×4 (附套件)						
	12	M12×1.75	M12×1.0	22	17	19										
	15	—	M15×1.0	25	21	22					10	6	—	—	—	
	16	M16×2.0	—													
	17	—	M17×1.0													
	20	M20×2.5	M20×1.0	35	26	30	13	8	2	M5×5 (附套件)						
	24	M24×3.0	—	43	33	35	15	10			—	—	—	—	—	—
	25	—	M25×1.5													
	30	M30×3.5	M30×1.5								48	39	40	20	14	
	35	—	M35×1.5	43	43	45										
40	M40×1.5		53	48	49	25	16									
50	M50×1.5		66	61	63											



型式	M×Pitch		D	C	止迴螺絲型					螺栓型										NT\$基準單價										
Type	M	粗螺紋	細螺紋		(e)	F	B	b	M ₁	(e) ₁	F ₁	B ₁	b ₁	M ₂	X	Y	Z	d	R	BNCM BNSC	BNSCC	BNCMS BNCS	BNBM BNBS	BNBSC	BNBMS BNBSS					
(粗螺紋止迴螺絲型) BNCM BNCMS	*5	M5×0.8	M5×0.5	9	19.6	17	9	5	M3	—	—	—	—	—	—	—	—	—	—	—		—			—	—				
	*6	M6×1.0	M6×0.75	10						—	—	—	—	—	—	—	—	—	—	—	—	—	—	—				—	—	
(粗螺紋螺栓型) BNBM BNBMS	8	M8×1.25	M8×1.0	13	21.9	19	10			27.7	24	13	9	M4	7	4	7 (8.5)	4.5	3.75											
	10	M10×1.5	M10×1.0	16						31.2	27				9		7 (10)													
(細螺紋止迴螺絲型) BNSC BNSCC BNSCS	12	M12×1.75	M12×1.0	17	27.7	24		6	M4	34.6	30	16	12	M5	9.5	4.5	9 (11)	5.5	4.5											
	15	—	M15×1.0	21						41.6	36				12.5	5	9.5 (12)													
(細螺紋螺栓型) BNBS BNBSC BNBSS	20	M20×2.5	M20×1.0	26	37.0	32				47.3	41	19	14	M6	15	6.5	12 (15)	7	5.5											
	24	M24×3.0	—	33											17	7.5	15													
	25	—	M25×1.5							53.1	46																			
	30	M30×3.5	M30×1.5	39						0.5	57.7	50			16	10	M6			57.7	50	20		19.5	8.5	18				

*M5・M6僅止迴螺絲型。  Z尺寸的()為不鏽鋼型。

