

附承板時規皮帶 (T5・T10)

—連結加工—

■特長：時規皮帶背面熔接承板,故可將各式工件以固定間距輸送。
■附承板時規皮帶適用於時規皮帶輪T5 適合 P.1451,T10適用於時規皮帶輪T10 適合 P.1453。

ATBT

●承板A B

●承板C (附攻牙孔)

●承板A形狀詳細

●承板A

●承板B

●承板C (附攻牙孔)

種類	Pitch	H	h	L
T5	5	2.2	1.2	1.8
T10	10	4.5	2.5	3.5

●承板A尺寸

種類	皮帶寬度	A	B	T	皮帶單位質量 g/m(寬度:10mm)	承板 重量(g)
T5	10mm	9	10	3	0.34	0.34
	15mm	14	10	3	0.52	0.52
	20mm	19	10	3	0.71	0.71
	25mm	24	10	3	0.89	0.89
T10	15mm	14	10	5	0.86	1.19
	20mm	19	10	5	1.17	1.55
	25mm	24	10	5	1.47	2.66
	30mm	29	15	5	2.67	3.15
	40mm	39	20	7	3.59	4.38
	50mm	49	20	7	6.02	5.61

●承板B尺寸

種類	皮帶寬度	A	B	d	G	F	T	皮帶單位質量 g/m(寬度:10mm)	承板 重量(g)
T5	10mm	9	10	3.5	5.5	—	—	0.30	0.30
	15mm	14	15	4.5	9	5	3	0.72	0.72
	20mm	19	15	4.5	9	5	3	0.94	0.94
	25mm	24	20	5.5	13	6	—	1.61	1.61
T10	15mm	14	15	4.5	9	—	—	1.19	1.19
	20mm	19	15	4.5	9	5	—	1.55	1.55
	25mm	24	20	5.5	13	6	—	2.66	2.66
	30mm	29	20	5.5	13	6	5	3.15	3.15
	40mm	39	20	6.5	13	7	—	4.38	4.38
	50mm	49	20	6.5	13	7	—	5.61	5.61

●承板C尺寸

種類	皮帶寬度	A	B	T	C	D	E	K	N	皮帶單位質量 g/m(寬度:10mm)	承板 重量(g)
T10	25mm	25.0	6.5	7.8	15.0	3.2	5.0	4.8	4.0	40.0	3.9

●承板安裝間距公差 (單位: mm)

安裝間距	安裝間距公差
30~200	±0.5
300~	±1.0

●承板尺寸公差 (單位: mm)

尺寸	尺寸公差
A	±0.5
B	±0.5
T	±0.5
C	±0.1

Example 使用範例

輸送物

治具

承板B

使用承板B可安裝適用於各種工件的治具。

輸送物

治具 (螺栓固定)

承板C

使用承板C時, 因為可以由上方以螺栓固定治具, 所以可安裝高度較低的治具或是特殊形狀的治具。

無縫環圈加工

將長度選擇型皮帶熱熔接加工為環狀。
連結加工部的芯線無接縫。

種類T5 (Pitch:5mm)

Type	型式	皮帶寬度 No.	承板 種類	承板 安裝間距 P	齒數	周長 (mm)	NTS本體基準單價1~5 pcs			
	皮帶 No.						皮帶寬度No.			
							100	150	200	250
ATBT	700T5	100 (10mm)	A	30 (指定單位50mm)	140	700				
	750T5				150	750				
	800T5				160	800				
	850T5				170	850				
	900T5				180	900				
	950T5				190	950				
	1000T5				200	1000				
	1050T5				210	1050				
	1100T5				220	1100				
	1150T5				230	1150				
	1200T5				240	1200				
	1250T5				250	1250				
	1300T5				260	1300				
	1350T5				270	1350				
	1400T5				280	1400				
	1450T5				290	1450				
	1500T5				300	1500				
	1550T5				310	1550				
	1600T5				320	1600				
	1650T5				330	1650				
	1700T5	340		1700						
	1750T5	350		1750						
	1800T5	360		1800						
	1850T5	370		1850						
	1900T5	380		1900						
	1950T5	390		1950						
	2000T5	400		2000						
	2050T5	410		2050						
	2100T5	420		2100						
	2150T5	430		2150						
	2200T5	440		2200						
	2250T5	450		2250						
	2300T5	460		2300						
	2350T5	470		2350						
	2400T5	480		2400						
	2450T5	490		2450						
	2500T5	500		2500						
	2550T5	510		2550						
	2600T5	520		2600						
	2650T5	530		2650						
2700T5	540	2700								
2750T5	550	2750								
2800T5	560	2800								
2850T5	570	2850								
2900T5	580	2900								
2950T5	590	2950								
3000T5	600	3000								
3050T5	610	3050								
3100T5	620	3100								
3150T5	630	3150								
3200T5	640	3200								
3250T5	650	3250								
3300T5	660	3300								
3350T5	670	3350								
3400T5	680	3400								
3450T5	690	3450								
3500T5	700	3500								
3550T5	710	3550								
3600T5	720	3600								
3650T5	730	3650								
3700T5	740	3700								
3750T5	750	3750								
3800T5	760	3800								
3850T5	770	3850								
3900T5	780	3900								
3950T5	790	3950								
4000T5	800	4000								

●承板安裝數量最少可為1個。
●承板指定為1個時,安裝間距請與皮帶No.相同。
●承板安裝間距請指定可以讓皮帶周長整除的數字。
(例) T5型,皮帶周長1050時
○ 1050÷30=35
○ 1050÷50=21
○ 1050÷100=10.5
○ 1050÷350=3
承板安裝間距
可指定30・50・350。
不可指定100。

Order 訂購範例	型式		承板 種類	承板 安裝間距 P
	Type	皮帶 No.		
	ATBT	1200T10	200	A
	ATBT	2450T10	300	C



●非型錄規格商品請參照 P.131
●CAD資料夾名稱: 19_Timing_Pulleys

種類T10 (Pitch:10mm)

Type	型式	皮帶寬度 No.	承板 種類	承板 安裝間距 P	齒數	周長 (mm)	NTS本體基準單價1～5 pcs					
	皮帶 No.						皮帶寬度No.					
							150	200	250	300	400	500
ATBT	700T10	150 (15mm)	A	50～2400 (指定單位50mm)	70	700						
	750T10				75	750						
	800T10				80	800						
	850T10				85	850						
	900T10				90	900						
	950T10				95	950						
	1000T10				100	1000						
	1050T10				105	1050						
	1100T10				110	1100						
	1150T10				115	1150						
	1200T10	120			1200							
	1250T10	125			1250							
	1300T10	130			1300							
	1350T10	135			1350							
	1400T10	140			1400							
	1450T10	145			1450							
	1500T10	150			1500							
	1550T10	155			1550							
	1600T10	160			1600							
	1650T10	165			1650							
	1700T10	170			1700							
	1750T10	175			1750							
	1800T10	180			1800							
	1850T10	185			1850							
	1900T10	190			1900							
	1950T10	195			1950							
	2000T10	200			2000							
	2050T10	205			2050							
	2100T10	210			2100							
	2150T10	215			2150							
	2200T10	220			2200							
	2250T10	225			2250							
	2300T10	230			2300							
	2350T10	235			2350							
	2400T10	240			2400							
	2450T10	245			2450							
	2500T10	250			2500							
	2550T10	255			2550							
	2600T10	260			2600							
	2650T10	265			2650							
2700T10	270	2700										
2750T10	275	2750										
2800T10	280	2800										
2850T10	285	2850										
2900T10	290	2900										
2950T10	295	2950										
3000T10	300	3000										
3050T10	305	3050										
3100T10	310	3100										
3150T10	315	3150										
3200T10	320	3200										
3250T10	325	3250										
3300T10	330	3300										
3350T10	335	3350										
3400T10	340	3400										
3450T10	345	3450										
3500T10	350	3500										
3550T10	355	3550										
3600T10	360	3600										
3650T10	365	3650										
3700T10	370	3700										
3750T10	375	3750										
3800T10	380	3800										
3850T10	385	3850										
3900T10	390	3900										
3950T10	395	3950										
4000T10	400	4000										