


BUSHINGS FOR LOCATING PINS -FLANGED TYPE-

定位銷用襯套

—附頭緣 標準・薄壁型—


● CAD資料夾名稱：22_Locating_Pins

■標準型



RoHS10

材質	表面處理	硬度	Type	
			p6	m6
相當於SKS3	—	60HRC～	JBH	JBHM
相當於SKS3	鍍無電解鍍	60HRC～	JBHN	JBHNM
相當於SUS440C	—	50HRC～	JBHC	JBHMC



●p6型內徑收縮程度較m6型大,進行孔加工時請留意。(請參考P.1727 壓入後的內徑變化表)

Type	d	型式		L選擇	壁厚(N)	R	H	T	D	D容許公差		NTS基準單價			
		無表面處理	鍍無電解鍍							p6	m6	JBH	JBHN	JBHC	JBHMC
(p6) JBH JBHM JBHC	2	+0.008 +0.002	+0.010 0	5 6 8 10 12	1.5	0.8	9	2.5	5	+0.020 +0.012	+0.012 +0.004				
	3			5 6 8 *10 12	2		11		7						
	4	+0.012 +0.004	+0.012 0	*5 6 8 10 12 15 *16 20	2		12		8	+0.024 +0.015	+0.015 +0.006				
	5			5 6 8 10 12 15 16 20	2.5	1			10						
	6			5 6 8 10 12 15 16 20 25	2		14		10						
	8				2		16		12						
	10	+0.014 +0.005	+0.014 +0.005	6 8 10 12 15 16 20 25	2.5		19	4	15	+0.029 +0.018	+0.018 +0.007				
	12			8 10 12 15 16 20 25 30	3	2	22		18						
	13			10 12 15 16 20 25 30	4.5		26		22						
	15	+0.017 +0.006	+0.017 +0.006	10 *12 *15 *16 *20 *25 *30	5		30	5	25	+0.035 +0.022	+0.021 +0.008				
(m6) JBHM JBHNM JBHMC	16			10 12 15 16 20 25 30	5		30		26						
	20			12 15 16 20 25 30	5		35		30						
	25	+0.020 +0.007	+0.020 +0.007	12 15 16 20 25 30	5	3	40	6	35	+0.042 +0.026	+0.025 +0.009				
				16 20 25 *30 35	5										

⊗L尺寸*僅JBHMC無法選擇


●鍍無電解鍍製品其d尺寸2～6的容許公差為H7。

■薄壁型



RoHS10

材質	表面處理	硬度	Type	
			p6	m6
SU2或相當於SKS3	—	58HRC～	JBHUP	JBHU
SU2或相當於SKS3	鍍無電解鍍	58HRC～	JBHUNP	JBHUN
相當於SUS440C	—	50HRC～	JBHUCP	JBHUC



●p6型內徑收縮程度較m6型大,進行孔加工時請留意。(請參考P.1727 壓入後的內徑變化表)

Type	d	型式		L選擇	壁厚(N)	R	H	T	D	D容許公差		NTS基準單價			
		無表面處理	鍍無電解鍍							p6	m6	JBHU	JBHUN	JBHUC	JBHUCP
(p6) JBHUP JBHUNP JBHUCP	3	+0.008 +0.002	+0.010 0	6 8 10 12			9	2.5	5	+0.020 +0.012	+0.012 +0.004				
	4			6 8 10 12 15 16			10		6						
	5	+0.012 +0.004	+0.012 0	6 8 10 12 *15 *16 20			11	3	7	+0.024 +0.015	+0.015 +0.006				
	6			6 8 10 12 *15 16 20			12		8						
	8			6 8 10 12 *15 16 20			14		10						
	10	+0.014 +0.005	+0.014 +0.005	6 8 10 12 *15 16 20			17	4	13	+0.029 +0.018	+0.018 +0.007				
	12			6 8 10 12 15 16 20	1.5		19		15						
	13			8 10 12 15 16 *20			21		17						
	15	+0.017 +0.006	+0.017 +0.006	10 12 15 16 20	2	1	24	5	19	+0.035 +0.022	+0.021 +0.008				
	16			12 15 16 20 *25	2.5		26		21						
(m6) JBHU JBHUN JBHUC	20			12 15 16 20 25			31		26						
	25	+0.020 +0.007	+0.020 +0.007	12 15 16 20 25		2	36	6	31	+0.042 +0.026	+0.025 +0.009				
				20 25											

⊗L尺寸*僅JBHUC無法選擇

●鍍無電解鍍製品其d尺寸3～6的容許公差為H7。

Order 訂購範例

型式	—	P	—	L
JBH5	—	8	—	12
JBHUN12	—			

Delivery 出貨日

WEB WOS

NTS Price 價格

WEB WOS

BUSHINGS FOR LOCATING PINS -FLANGED TYPE-


定位銷用襯套

—自由指定附頭緣 標準・薄壁型—

● CAD資料夾名稱：22_Locating_Pins


■特長：內徑可以0.01mm為單位, L尺寸可以0.1mm為單位指定的襯套。

■標準型



RoHS10

材質	表面處理	硬度	Type	
			p6	m6
相當於SKS3	—	56～60HRC	JBHF	JBHF
相當於SKS3	染黑處理	56～60HRC	JBHF	JBHF
相當於SKS3	鍍無電解鍍	56～60HRC	JBHF	JBHF
SUS304	—	—	JBHF	JBHF
相當於SUS440C	—	50～55HRC	JBHF	JBHF




●p6型內徑收縮程度較m6型大,進行孔加工時請留意。(請參考P.1727 壓入後的內徑變化表)

Type	D	D容許公差		指定單位0.01mm	指定單位0.1mm	壁厚(N)	R	H	T	NTS基準單價			
		p6	m6							JBHF	JBHF	JBHF	JBHF
(p6) JBHF JBHF JBHF JBHF	5	+0.022 +0.012	+0.012 +0.004	2.20～2.50	3.0～3.5	1.25～1.50		9	2.5				
	7			2.20～3.50	3.0～6.0	1.75～2.50		11					
	8	+0.024 +0.015	+0.015 +0.006	3.00～4.50	3.0～10.0			12	3				
	10			4.00～6.50				14					
	12			6.00～8.50				16					
	15	+0.029 +0.018	+0.018 +0.007	8.00～10.50				19	4				
	18			10.00～12.50				22					
	20			12.00～13.50				26					
	22			12.00～13.50	5.0～35.0			30	5				
	25	+0.035 +0.022	+0.021 +0.008	13.00～15.50				35	6				
(m6) JBHF JBHF JBHF JBHF	26			15.00～16.50				40					
	30			16.00～20.50									
	35	+0.042 +0.026	+0.025 +0.009	20.00～25.00	5.0～50.0								

●P≤3.59則L+T≤P×2.5


●P≥3.60則L+T≤P×3.0

■薄壁型



RoHS10

材質	表面處理	硬度	Type	
			p6	m6
相當於SKS3	—	56～60HRC	JBHUF	JBHUF
相當於SKS3	染黑處理	56～60HRC	JBHUF	JBHUF
相當於SKS3	鍍無電解鍍	56～60HRC	JBHUF	JBHUF
相當於SUS440C	—	50～55HRC	JBHUF	JBHUF



●p6型內徑收縮程度較m6型大,進行孔加工時請留意。(請參考P.1727 壓入後的內徑變化表)

Type	D	D容許公差		指定單位0.01mm	指定單位0.1mm	壁厚(N)	R	H	T	NTS基準單價			
		p6	m6							JBHUF	JBHUF	JBHUF	JBHUF
(p6) JBHUF JBHUF JBHUF JBHUF	7			3.51～5.00	3.0～6.0	1.00～1.74		11	2.5				
	8	+0.024 +0.015	+0.015 +0.006	4.51～6.00	3.0～10.0	1.25～2.24		12					
	9			4.51～6.50		1.00～1.74		13.5	3				
	10			6.51～8.00		1.00～1.74		14					
	11			8.00～9.00	3.0～15.0	1.00～1.50		15					
	12			8.51～9.00		1.50～1.74		16					
	13	+0.029 +0.018	+0.018 +0.007	8.51～10.00		1.50～2.24		17	4				
	14			9.00～11.00		1.50～2.50		18					
	15			10.51～12.00		1.50～2.24		19					
	17			10.51～13.00		2.00～3.24		21					
(m6) JBHUF JBHUF JBHUF JBHUF	18			12.51～14.00	5.0～35.0	2.00～2.74		22					
	20			13.51～15.00		2.50～3.24		26	5				
	22			13.51～17.00		2.50～4.24		30					
	25	+0.035 +0.022	+0.021 +0.008	15.51～19.00		3.00～4.74		35	6				
	26			16.51～20.00		3.00～4.74		40					
	30			20.51～24.00		3.00～4.99							
	35	+0.042 +0.026	+0.025 +0.009	25.01～29.00	5.0～50.0								

●P≤3.59則L+T≤P×2.5

●P≥3.60則L+T≤P×3.0

Order 訂購範例

型式	—	P	—	L
JBHFM25	—	P14.00	—	L20.0
JBHUFM15	—	P11.00	—	L20.0

Delivery 出貨日

WEB WOS

NTS Price 價格

WEB WOS

Alteration 追加加工

型式	—	P	—	L	(RC・TC)
JBHFM12	—	P8.00	—	L12.0	RC

Alterations	Code	Spec.
內徑R追加	RC	在兩側加工內徑R。 適用於壁厚1.5mm以上 D10以上的R尺寸與頭緣側的R相同。 指定方法 RC
頭緣厚度變更	TC	指定單位1mm 指定方法 TC4 3≤TC<T ●全長T—TC部分縮短。 ●適用於D≥12