

銅管/銅管用接頭

CAD資料夾名稱：51\_Pipes\_Fitting\_Valves

■銅管



RoHS

| Type | M 材質        | 規格           |
|------|-------------|--------------|
| DKE  | 磷酸銅 (C1220) | JIS H : 3300 |



✓( 25 / )

| 型式   |    | L       |  | t | NTS基準單價     |              |              |              |              |               |
|------|----|---------|--|---|-------------|--------------|--------------|--------------|--------------|---------------|
| Type | D  | 指定單位1mm |  |   | L10<br>~100 | L101<br>~200 | L201<br>~400 | L401<br>~600 | L601<br>~800 | L801<br>~1000 |
| DKE  | 3  | 10~250  |  | 1 |             |              |              |              |              |               |
|      | 4  |         |  |   |             |              |              |              |              |               |
|      | 5  | 10~500  |  |   |             |              |              |              |              |               |
|      | 6  |         |  |   |             |              |              |              |              |               |
|      | 8  |         |  |   |             |              |              |              |              |               |
|      | 10 |         |  |   |             |              |              |              |              |               |
|      | 12 | 10~900  |  |   |             |              |              |              |              |               |
|      | 14 |         |  |   |             |              |              |              |              |               |
|      | 15 |         |  |   |             |              |              |              |              |               |
|      | 16 | 10~1000 |  |   |             |              |              |              |              |               |
|      | 18 |         |  | 2 |             |              |              |              |              |               |

■D尺寸・L尺寸公差

| 以上  | 以下   | D    | L    |
|-----|------|------|------|
| 3   | 6    | ±0.1 | ±0.1 |
| 7   | 30   | ±0.2 | ±0.2 |
| 31  | 120  | ±0.3 | ±0.3 |
| 121 | 400  | ±0.5 | ±0.5 |
| 401 | 1000 | ±0.8 | ±0.8 |

Order 訂購範圍

Delivery 出貨日

Price 價格

NTS

WEB WOS


形式

DKE10

L


300

■銅管用接頭  
—外螺牙連接型—



RoHS

DKPT



M 材質 黃銅

| 型式   |        | T         | R (PT) | 約L | L1 | L2 | T1     | 對邊    | NTS基準單價 |
|------|--------|-----------|--------|----|----|----|--------|-------|---------|
| Type | 適用管外徑D | R (PT) 選擇 | R (PT) |    |    |    | G (PF) | 本體 螺帽 |         |
| DKPT | 3      | 1         | 1/8    | 28 | 5  | 9  | 1/8    | 12 12 |         |
|      |        | 2         | 1/4    | 32 | 6  | 12 | 1/8    | 14 12 |         |
|      | 4      | 1         | 1/8    | 28 | 5  | 9  | 1/8    | 12 12 |         |
|      |        | 2         | 1/4    | 32 | 6  | 12 | 1/8    | 14 12 |         |
|      | 5      | 1         | 1/8    | 28 | 5  | 9  | 1/8    | 12 12 |         |
|      |        | 2         | 1/4    | 32 | 6  | 12 | 1/8    | 14 12 |         |
|      | 6      | 1         | 1/8    | 33 | 6  | 9  | 1/4    | 14 16 |         |
|      |        | 2         | 1/4    | 36 | 6  | 12 | 1/4    | 16 16 |         |
|      |        | 3         | 3/8    | 39 | 8  | 13 | 1/4    | 19 16 |         |
|      | 8      | 1         | 1/8    | 33 | 6  | 9  | 1/4    | 14 16 |         |
|      |        | 2         | 1/4    | 36 | 6  | 12 | 1/4    | 16 16 |         |
|      |        | 3         | 3/8    | 39 | 8  | 13 | 1/4    | 19 16 |         |
|      | 10     | 2         | 1/4    | 40 | 8  | 12 | 3/8    | 19 19 |         |
|      |        | 3         | 3/8    | 41 | 8  | 13 | 3/8    | 19 19 |         |
|      |        | 4         | 1/2    | 46 | 10 | 16 | 3/8    | 22 19 |         |
|      | 12     | 2         | 1/4    | 46 | 10 | 12 | 1/2    | 22 24 |         |
|      |        | 3         | 3/8    | 47 | 10 | 13 | 1/2    | 22 24 |         |
|      |        | 4         | 1/2    | 50 | 10 | 16 | 1/2    | 24 24 |         |
|      | 14     | 3         | 3/8    | 48 | 10 | 13 | 1/2    | 22 24 |         |
|      |        | 4         | 1/2    | 51 | 10 | 16 | 1/2    | 24 24 |         |
|      | 15     | 3         | 3/8    | 50 | 10 | 13 | 5/8    | 24 27 |         |
|      |        | 4         | 1/2    | 54 | 11 | 16 | 5/8    | 27 27 |         |
|      | 16     | 3         | 3/8    | 50 | 10 | 13 | 5/8    | 24 27 |         |
|      |        | 4         | 1/2    | 54 | 11 | 16 | 5/8    | 27 27 |         |