




S50C尺寸固定板

—6面銑面/6面銑面上下面旋轉式研磨—



■6面銑面

型式	A	B	T	5	6	8	9	10	12	13	15	16	19	20	22	25	28	30	34	35	40	50									
SC6F	60	60	60																												
		80	60																												
		100	60																												
		125	60																												
		150	60																												
	80	160	80																												
		200	80																												
		250	80																												
		300	80																												
		350	80																												
		100	400	100																											
			450	100																											
			500	100																											
			125	125																											
			150	150	150																										
	160	150																													
	200	150																													
	250	150																													
	300	150																													
	160	350		150																											
400		160																													
450		160																													
500		160																													
200		200																													
250	250	200																													
	300	200																													
	350	200																													
	400	200																													
	450	200																													
	300	500	200																												
		300	300																												
		350	300																												
		400	300																												
		450	300																												

Order 訂購規格	型式	A	B	T
	SC6F	100	100	8
	SCAH	100	100	8



■精密度基準

(最大值)

項目	SC6F	SCAH
板厚平行度(每100mm)	0.05	0.012
平面度(每100mm)	T5·6	0.1
	T8~15	0.07
	T16~25	0.05
	T28~50	0.012
基準面直角度	每100mm為0.015	
外圍倒角	C0.2~C0.5	C0.5~C1.0



■6面銑面上下面旋轉式研磨

型式	A	B	T	5·6	8·9	10	12·13	15·16	19·20	22	25	28	30	34·35	40	50																
SCAH	60	60	60																													
		80	60																													
		100	60																													
		125	60																													
		150	60																													
	80	160	80																													
		200	80																													
		250	80																													
		300	80																													
		350	80																													
		100	400	100																												
			450	100																												
			500	100																												
			125	125																												
			150	150	150																											
	160	150																														
	200	150																														
	250	150																														
	300	150																														
	160	350		150																												
400		160																														
450		160																														
500		160																														
200		200																														
250	250	200																														
	300	200																														
	350	200																														
	400	200																														
	450	200																														
	300	500	200																													
		300	300																													
		350	300																													
		400	300																													
		450	300																													