一桿型-


**BIG ORDER** 

## 支撐架

-精巧型・L型-

CAD資料夾名稱: 55\_Cylinders






型式		h												NT\$基準單價			
Туре	D	HLRB HLRBSW	HLRBH 單位1mm	В	D <sub>1</sub>	Т	容許公差	W	H*	а	l	Р	d	HLRB	HLRBSW	HLRBH	
	4		6~20	6	4.5			16	24	4		8					
高度·固定型 HLRB HLRBSW 高度·指定型 HLRBH	6	14	5~19	8	6.5	4		10	25	5	6	0	4.5				
	7		7~18	10	8		0.12	19	26	6		10					
	8	18	7~25	12	9	6		22	33	7	8	12	5.5				
	10		9~24	14	11	O		25	34	8	0	14	5.5				
	13	25	12~30	17	14	0	0 -0.15	32	45	10	10	20 26	6.6				
	16	25	13~28	21	18	0		38	47	12	10	26					
	18	- 30	19~34	23	20	10	0 -0.18	50	56	14	10	34	9				
	21		18~33	26	23	12		50	57	15	12						
	25	40	21~46	30	27	15	0	65	7/	10	15	11	11				

\*高度h指定型為H=a+h+ℓ。 





■頂端/底部安裝



型式			h													N	T\$基準單(	Ę .
Туре		D	HLRD 固定	HLRDH·HLRDBH 指定單位1mm	Н	В	D <sub>1</sub>	Т	容許公差	W	Р	d	d1	H <sub>1</sub>	М	HLRD	HLRDH	HLRDBH
頂端安裝		7	9	10~24	h+6	10	8	8	0	36	26	4.5			4			
高度h固定型	高度h指定型 HLRDH	8	11	12~23	h+7	12	9	10	<b>一</b> 0.15	42	30	г.г	_	-	_			
HLRD		10	12	13~27	h+8	14	11	12	0	44	32	5.5	9.5	5.5	5			
		13	14	15~30	h+10	17	14	13	<b>-</b> 0.18	52	38			<u>с</u> г				
底部安裝		16	18	19~33	h+12	21	18	8 15		56	42	6.6	11	6.5	6			
	高度h指定型	18	20	21~36	h+14	23	20	16	0	66	48	9	-14	_	0			
HLRDBH		21	21	22~35	h+15	26	23	19	-0.22	70	52	9	14	9	8			
		25	24	25~41	h+19	30	27	20		84	62	11	17	11	10			

































Example 使用範例

氣壓缸桿



型式	н	В	D <sub>1</sub>	т		w		Р	s	d	NT\$基準單價	
Type	D	п		וטו	•		_ vv	а	-	3	u	14   少空学早頃
	7	20	10	8	6	19	22	6	10	14	4.5	
	8	25	12	9		22		7	12		5.5	
	10	25	14	11		25		8	14		5.5	
HLRL	13	30	17	14		32		10	20		6.5	
HLNL	16		21	18	- 8	38	32	12	26	20	0.5	
	18	35	23	20	0	50	32	14	34	20	9	
	21	40	26	23	10	50	40	15	34	25	9	
	25	45	30	27		60		19	40	20	11	







