-兩面加工型-




## HINGE PINS -FEMALE THREAD BOTH ENDS TYPE · MALE THREAD BOTH ENDS TYPE-鉸鏈銷

-兩端內螺牙型·兩端外螺牙型-









型式		<b>3</b> L	指定單位1mm		N
Type	<b>2</b> D	指定單位0.1mm	<b>4</b> F	<b>6</b> T	N
CLSW CLSWH SCLSW	4	10.0~50.0	2≦F≦20	2≦T≦20	0.5
	5	10.0~60.0	2≦F≦20		
	6	10.0~100.0	2≦F≦30	2≦T≦30	1
	8	10.0~100.0			
	10	15.0~100.0			
	12	15.0~200.0		5≦T≦30	
	15	25.0~200.0			
	16		5≦F≦30		2
	20	30.0~200.0			
	25				



12 | 支點用軸頸螺絲







₹僅適用於當日PM1:30前提出申請之訂單 超過PM1:30之訂單出貨日+1日。

MiSUMi e-Catalog

數量區分		特殊訂購					
数里四万	少量		大量				
數量	1~19	20~49	50~200	201~300	301~		
出貨日	一般	+2日	+7日	+14日	交期另估		
● 招級表由是大動量時亦加早仕 ■ P B							



搜尋人



726