


MEFLL300 ($\theta = 35-65$)



W	θ	A	B	C	E	F	H	x
300	35	345.03	360.03	15	160.19	194.81	220	159
	40	337.97	372.97	35	173.41	181.59	240	170
	45	334.71	384.71	50	187.72	167.28	260	174
	50	325.15	395.15	70	203	152	280	181
	55	314.23	404.23	90	219.12	135.88	295	185
	60	306.87	411.87	105	235.98	119.02	315	184
	65	298	418	120	253.44	101.56	340	183

行程 S	加工力kN (tonf)		弹力N (kgf)			总重量 kg	Catalog No.	W	θ
	标准加工力	极限加工力	初压	下死点前5mm	终压				
57.3	294.2 (30.0)	588.4 (60.0)	1725 (175.9)	12961(1321.6)	14045 (1432.2)	178.7	MEFLL	300	35
63.0				13059(1331.7)					40
69.6				13158(1341.7)					45
77.4				13256(1351.8)					50
87.1				13330(1359.3)					55
99.6				13429(1369.4)					60
116.5		13527(1379.4)	65						

Order 订货范例 Catalog No. W - θ
MEFLL 300 - 60

Delivery 交货期 另 询交货期

Price 价格 询价联系方式:
WOS: <https://www.misumi-ec.com/cn/> P.57
TEL: 021-6710-8701 / FAX: 021-6710-8984 P.1663

Alterations 追加加工 Catalog No. W - θ - (K · KA) MEFLL 300 - 60 - KA 另 询交货期

Alterations	Code	Spec.
	K	追加定位键(6个) (带6个M8×15内六角螺钉) 附属键
	KA	追加台阶型定位键(6个) (带6个M8×15内六角螺钉) 附属键