




一定位预孔 - MEDC100 ($\theta = 05 - 20$)
 一定位精加工孔 - MEDCA100 ($\theta = 05 - 20$)



■斜楔行程关系图 P.1333
 ■构成零件表 P.1335

W	θ	S	A	E	F	H	H ₁	J	N	U	a	a ₁	c	c ₁	e	f	g	h	h ₁	x
100	05	45	172.22	54.72	145.28	155.6	140	35	199.22	27.5	160	100	90	50	17.5	140	40	105	60	98
		70	207.08	52.77	147.23	161.1	160	40	234.08	30	190	120	70	60	12.5	150	45	130	80	90
	10	45	178.12	65.02	134.98	156.8	140	35	205.12	30	160	100	90	50	17.5	140	40	105	60	103
		70	212.59	66.1	133.9	161.6	160	40	239.59	35	190	120	70	60	12.5	150	45	130	80	95
	15	45	182.67	70.77	129.23	160	125	40	209.67	32.5	160	110	90	55	17.5	140	40	105	70	106
		70	216.48	69.83	130.17	171.5	130	40	243.48	35	190	130	70	65	12.5	150	45	130	90	98
20	45	185.83	81.86	118.14	161.2	120	40	212.83	35	160	110	90	55	17.5	140	40	105	70	109	
	70	218.72	78.83	121.17	179.5	130	40	245.72	45	190	130	70	65	12.5	150	45	130	90	98	

加工力KN (tonf)		弹簧力N (kgf)			总重量 kg	Catalog No.	W	θ	行程 S	
标准加工力	极限加工力	初压	下死点前5mm	终压						
39.2 (4.0)	78.5 (8.0)	263 (26.8)	1015 (103.5)	1109 (113.1)	33.0	一定位预孔 - MEDC 一定位精加工孔 - MEDCA	100	05	45	
		194 (19.8)	1065 (108.6)	1132 (115.5)	38.0				70	
		263 (26.8)	1015 (103.5)	1109 (113.1)	33.0				10	45
		194 (19.8)	1065 (108.6)	1132 (115.5)	38.0					70
		263 (26.8)	1015 (103.5)	1109 (113.1)	32.0				15	45
		194 (19.8)	1065 (108.6)	1132 (115.5)	38.0					70
	263 (26.8)	1015 (103.5)	1109 (113.1)	39.0	20	45				
	194 (19.8)	1065 (108.6)	1132 (115.5)	39.0		70				

Order 订货范例 Catalog No. W - θ - S
 MEDCA 100 - 15 - 70

Delivery 交货期
 • MEDCA 100-05-45
 • MEDCA 100-10-45
 • MEDCA 100-10-70
 • MEDCA 100-20-45
 • 左述以外
 22 天发货
 隔日上海·广州发货 P.41
 上海·广州发货
 数量≥5时, 请另询交货期。
 数量≥5时, 请另询交货期。

Price 价格
 询价联系方式:
 WOS: <https://www.misumi-ec.com/cn/> P.57
 TEL: 021-6710-8701 / FAX: 021-6710-8984 P.1663

Alterations 追加加工 Catalog No. W - θ - S - (N)
 MEDCA 100 - 10 - 45 - N12
 另 询交货期

Alteration	Code	Spec.
	N12	变更定位销孔径 $\phi 13H7 \Rightarrow \phi 12H7$ ⊗ 定位预孔型不适用