



ノックピン 定位销




MS (直杆型)




M 材质 SUJ2
H 硬度 58HRC~

MSV (高精度型)




M 材质 SUJ2
H 硬度 58HRC~

MSTP (带拉拔螺纹精密型)




Ⓢ D5 · 6且L尺寸为10时，螺纹底孔有时会贯通。
M 材质 SUJ2
H 硬度 58HRC~

MST (带拉拔螺纹p6型)



Ⓢ D5 · 6且L尺寸为10时，螺纹底孔有时会贯通。



M 材质 SUJ2
H 硬度 45~50HRC

Ⓢ ℓ₁、ℓ₂尺寸为参考值。由于是外圆磨加工，有时会比下表所记尺寸要大。

ℓ ₁	Catalog No.		L															
	Type	D																
0.4	MS	1	6	8	10													
		1.5	6	8	10													
0.6	MS	2	6	8	10	15	20											
		2.5	6	8	10	15	20	25	30									
		3	6	8	10	15	20	25	30	35	40							
		4	8	10	15	20	25	30	35	40	45	50						
1.0	MS	5	8	10	15	20	25	30	35	40	45	50						
		6	8	10	15	20	25	30	35	40	45	50	55	60				
1.5	MS	8	10	15	20	25	30	35	40	45	50	55	60	65	70	80		
		10	15	20	25	30	35	40	45	50	55	60	65	70	80			
2.0	MS	12	20	25	30	35	40	45	50	55	60	70	80					
		13	30	40	50	60	70	80										

ℓ ₁	ℓ ₂	Catalog No.		L															
		Type	D																
1.0	0.2	MSV	2	6	8	10													
			3	8	10	15	20	25	30										
			4	10	15	20	25	30											
1.5	0.5	MSV	5	10	15	20	25	30											
			6	10	15	20	25	30											
2.0	0.5	MSV	8	20	30	40													
			10	30	40	50	60												

Ⓢ 高精度型定位销是在恒温室内测量的。


ℓ ₁	M×P	ℓ	D	Catalog No.		L															
				Type	D																
1.5	3×0.5	*6	+0.010 +0.005	MSTP	5	10	15	20	25	30											
					6	10	15	20	25	30	35	40	50								
2.0	4×0.7	*8	+0.010 +0.005	MSTP	8	15	20	25	30	35	40	45	50	60	70	80					
					10	15	20	25	30	35	40	45	50	60	70	80					
2.5	6×1.0	10	+0.010 +0.005	MSTP	12	20	30	40	50	60	70	80									
					13	40	50	60	70	80											
3.0	8×1.25	15	+0.010 +0.005	MSTP	16	40	50	60	70												

Ⓢ *D=5时，ℓ=6为参考值 Ⓢ *仅D=6、L=10时，ℓ=6


ℓ ₁	ℓ ₂	M×P	ℓ	Dp6	Catalog No.		L															
					Type	D																
1.5	0.5	3×0.5	*6	+0.020 +0.012	MST	5	10	15	20	25	30											
						6	10	15	20	25	30	35	40	50								
2.0	0.7	4×0.7	*8	+0.024 +0.015	MST	8	15	20	25	30	35	40	45	50	60	70	80					
						10	15	20	25	30	35	40	45	50	60	70	80					
2.5	1.0	6×1.0	10	+0.029 +0.018	MST	12	20	30	40	50	60	70	80									
						13	40	50	60	70	80											
3.0	1.0	8×1.25	15	+0.029 +0.018	MST	16	40	50	60	70	80											
						20	50	60	70	80												
3.0	1.5	10×1.5	18	+0.035 +0.022	MST	20	50	60	70	80												

Ⓢ *D=5时，ℓ=6为参考值 Ⓢ *仅D=6、L=10时，ℓ=6

MSTM (带拉拔螺纹m6型)




Ⓢ D5 · 6且L尺寸为10时，螺纹底孔有时会贯通。




M 材质 SUJ2
H 硬度 45~50HRC

MTT (带拉拔螺纹锥型)



M 材质 SK4
H 硬度 45~50HRC

MSTH (带拉拔螺纹h7型)



Ⓢ D5 · 6且L尺寸为10时，螺纹底孔有时会贯通。
D10且L尺寸为15时，螺纹底孔有时会贯通。

M 材质 SUJ2
H 硬度 45~50HRC

Ⓢ ℓ₁、ℓ₂尺寸为参考值。由于是外圆磨加工，有时会比下表所记尺寸要大。

ℓ ₁	ℓ ₂	M×P	ℓ	Dm6	Catalog No.		L															
					Type	D																
1.5	0.3	3×0.5	*6	+0.012 +0.004	MSTM	5	10	15	20	25	30											
						6	10	15	20	25	30	35	40	50								
2.0	0.5	4×0.7	*8	+0.015 +0.006	MSTM	8	15	20	25	30	35	40	45	50	60	70	80					
						10	15	20	25	30	35	40	45	50	60	70	80					
2.5	1.0	6×1.0	10	+0.018 +0.007	MSTM	12	20	30	40	50	60	70	80									
						13	40	50	60	70	80											
3.0	1.5	8×1.25	15	+0.021 +0.008	MSTM	16	40	50	60	70	80											
						20	50	60	70	80												

Ⓢ *D=5时，ℓ=6为参考值 Ⓢ *仅D=6、L=10时，ℓ=6

M×P	ℓ	Catalog No.		L			
		Type	D				
5×0.8	9	MTT	8	30	40		
6×1.0	10		10	40	50		
8×1.25	14		12	40	50		
10×1.5	16		13	50	60		
			16	60	70		

ℓ ₁	ℓ ₂	M×P	ℓ	Dh7	Catalog No.		L															
					Type	D																
1.5	0.3	3×0.5	*6	0 -0.012	MSTH	5	10	15	20	25	30											
						6	10	15	20	25	30	35	40	50								
2.0	0.5	4×0.7	*8	0 -0.015	MSTH	8	15	20	25	30	35	40	45	50	60	70	80					
						10	15	20	25	30	35	40	45	50	60	70	80	100	120			
2.5	1.0	6×1.0	10	0 -0.018	MSTH	12	20	30	40	50	60	70	80	100	120							
						13	40	50	60	70	80	100	120									
3.0	1.5	8×1.25	15	0 -0.018	MSTH	16	40	50	60	70	80	100	120	150								

Ⓢ *D=5时，ℓ=6为参考值 Ⓢ *仅D=6、L=10时，ℓ=6



Order 订货范围

Catalog No. - L
MS 2 - 20



Delivery 交货期

库存品

Ⓢ 隔日上海·广州发货 P.41 (17:00前订购的库存品可当日发货。)
Ⓢ 数量≥4001时，请另询交货期。
Ⓢ MSTM数量≥2000时，请另询交货期。
Ⓢ MSTH数量≥601时，请另询交货期。




Price 价格

询价联系方式：
WOS: <https://www.misumi-ec.com/cn/> P.57
TEL: 021-6710-8701 / FAX: 021-6710-8984 P.1663

Ⓢ 套装销售详情请参阅 P.803 · 804

通气面深度 Ⓢ 因为是滚筒抛光，仅作为参考值。



所有D尺寸采用同一深度
涉及品种: MSTP
MST
MSTM
MSTH