

M×P	S	B	C	Catalog No.		L 指定单位10mm
				Type	D	
10×1.5	15	8	5	RCUP	16	50 ~ 100
						110 ~ 150
						160 ~ 200
12×1.75	18	10	6	RCUP	20	50 ~ 100
						110 ~ 150
						160 ~ 200
16×2.0	24	14	9	RCUP	25	50 ~ 100
						110 ~ 150
						160 ~ 200
20×2.5	30	17	12	RCUP	32	50 ~ 100
						110 ~ 150
						160 ~ 200

RCUP的外螺纹内径比MCUP大1个级别。




Catalog No. — L
RCUP 20 — 200

7 天发货
上海·广州发货
数量≥101时，请另询交货期。

Catalog No. — L(LC) — (LKC)
RCUP 200 — LC195 — LKC

Alterations	Code	Spec.
	LC	变更全长 35 ≤ LC < L 指定单位1mm
	LKC	变更全长公差 L公差 -0.1 → -0.04 LC → 指定单位0.1mm (LC并用时, LC指定单) 位可为0.1mm



H	Catalog No.		L 指定单位10mm
	Type	D	
15	HCUP	10	50 ~ 100
			110 ~ 150
			160 ~ 200
18	HCUP	13	50 ~ 100
			110 ~ 150
			160 ~ 200
21	HCUP	16	50 ~ 100
			110 ~ 150
			160 ~ 200
25	HCUP	20	50 ~ 100
			110 ~ 150
			160 ~ 200
30	HCUP	25	50 ~ 100
			110 ~ 150
			160 ~ 200
37	HCUP	32	50 ~ 100
			110 ~ 150
			160 ~ 200




Catalog No. — L
HCUP 13 — 150

7 天发货
上海·广州发货
数量≥101时，请另询交货期。

Catalog No. — L(LC) — (LKC·MC·NC)
HCUP 13 — LC155 — LKC

Alterations	Code	Spec.													
	LC	变更全长 35 ≤ LC < L 指定单位1mm													
	LKC	变更全长公差 L公差 -0.1 → -0.04 LC → 指定单位0.1mm (LC并用时, LC指定单) 位可为0.1mm													
	MC	螺纹加工 <table border="1"> <tr> <th>D</th> <th>M</th> <th>ℓ</th> </tr> <tr> <td>10</td> <td>6</td> <td rowspan="3">2×M</td> </tr> <tr> <td>13-16</td> <td>8</td> </tr> <tr> <td>20</td> <td>10</td> </tr> <tr> <td>25-32</td> <td>12</td> <td></td> </tr> </table>	D	M	ℓ	10	6	2×M	13-16	8	20	10	25-32	12	
D	M	ℓ													
10	6	2×M													
13-16	8														
20	10														
25-32	12														
	NC	螺纹加工 <table border="1"> <tr> <th>D</th> <th>M</th> <th>ℓ</th> </tr> <tr> <td>10</td> <td>6</td> <td rowspan="3">2×M</td> </tr> <tr> <td>13-16</td> <td>8</td> </tr> <tr> <td>20</td> <td>10</td> </tr> <tr> <td>25-32</td> <td>12</td> <td></td> </tr> </table>	D	M	ℓ	10	6	2×M	13-16	8	20	10	25-32	12	
D	M	ℓ													
10	6	2×M													
13-16	8														
20	10														
25-32	12														



M×P	S	B	F	Catalog No.		L 指定单位10mm
				Type	D	
8×1.25	12	13	16	MCUP	16	50 ~ 100
						110 ~ 150
						160 ~ 200
10×1.5	15	16	16	MCUP	20	50 ~ 100
						110 ~ 150
						160 ~ 200
12×1.75	18	18	16	MCUP	25	50 ~ 100
						110 ~ 150
						160 ~ 200
16×2.0	24	21	16	MCUP	32	100 ~ 150
						160 ~ 200
						210 ~ 250



Catalog No. — L
MCUP 20 — 200

7 天发货
上海·广州发货
数量≥101时，请另询交货期。

Catalog No. — L(LC) — (LKC·MC)
MCUP 20 — LC195 — LKC

Alterations	Code	Spec.													
	LC	变更全长 35 ≤ LC < L 指定单位1mm													
	LKC	变更全长公差 L公差 -0.1 → -0.04 LC → 指定单位0.1mm (LC并用时, LC指定单) 可为0.1mm													
	MC	螺纹加工 <table border="1"> <tr> <th>D</th> <th>M</th> <th>ℓ</th> </tr> <tr> <td>16</td> <td>8</td> <td rowspan="3">2×M</td> </tr> <tr> <td>20</td> <td>10</td> </tr> <tr> <td>25</td> <td>12</td> </tr> <tr> <td>32</td> <td>16</td> <td></td> </tr> </table>	D	M	ℓ	16	8	2×M	20	10	25	12	32	16	
D	M	ℓ													
16	8	2×M													
20	10														
25	12														
32	16														

小物部品
铸件金型用

小物部品
铸件金型用