



ガスプリング用プレート ー上溝固定タイプー
氮气弹簧用板
 ー上槽固定型ー

RoHS10

FCC **FC19・25**

材 质 相当于S45C
 S 表面处理 四氧化三铁保护膜(Fe₃O₄)

RoHS10

FC32~195
FCB

材 质 相当于S45C
 S 表面处理 四氧化三铁保护膜(Fe₃O₄)

A	a	B	d	t	h			Catalog No.	适用氮气弹簧					建议螺栓 2个	
					GSV	GSSC	GSU		GSV	GST	GSH	GSK	GSSC		GSU
34	24	21	6.6	9	-	-	21.5	FCC	12	-	-	-	-	50	CB6-18
37	27	24	6.6	9	-	-	21.5		15	-	-	-	-	70	CB6-18
44	32	25	6.6	9	21.5	-	21.5		19	170	-	-	-	90	CB6-18
50	38	30	6.6	9	21.5	18	21.5		25	320	-	-	400	200	CB6-18

FCC符合VDI 3003标准。

A	a	B	b	d	t	h			Catalog No.	适用氮气弹簧					建议螺栓 4个			
						GSV GST GSK	GSH	GSSC		GSU	GSV	GST	GSH	GSK		GSSC	GSU	
44	30	25	12	6.6	9	21.5	-	-	21.5	FC	19	170	-	-	-	90	CB6-18	
50	34	30	18	6.6	9	21.5	-	18	21.5		25	320	-	-	400	200	CB6-18	
60	-	35	-	7	9	17	-	16	15		32	350	350	-	150	750	300	CB6-18
68	-	40	-	7	9	17	-	15	-		38	500	500	-	250	1000	-	CB6-18
86	-	50	-	9	13	23	-	-	-		45	750	750	-	500	-	-	CB8-25
95	-	56.5	-	9	13	24	22	-	-		50	1000	1000	1000	750	-	-	CB8-25
122	-	73.5	-	11	16	27	27	-	-		63	1500	1500	1500	-	-	-	CB10-35
122	-	73.5	-	11	16	29	29	-	-		75	2400	2400	2400	1500	-	-	CB10-35
150	-	92	-	13.5	18	33	33	-	-		95	4200	4200	4200	3000	-	-	CB12-40
175	-	109.5	-	13.5	21	36	36	33	-		120	6600	6600	6600	5000	12000	-	CB12-40
220	-	138	-	17.5	27	41	-	38	-		150	9500	12000	9500	-	7500	18500	CB16-55
290	-	170	-	17.5	27	47	-	-	-		195	20000	-	-	5000	-	-	CB16-55

FC19~195符合ISO 11901-2标准。(※FC63除外)

A	B	d	t	h	Catalog No.	适用氮气弹簧 GSSC	建议螺栓 4个
95	56.5	9.0	13	21	FCB	50	1800
122	73.5	11.0	16	27		63	3000
122	73.5	11.0	16	26		75	4700
150	92.0	13.5	18	30		95	7500

RoHS10

FCQ **FCQB**

材 质 相当于S45C
 S 表面处理 四氧化三铁保护膜(Fe₃O₄)

A	a	d	g	Catalog No.	适用氮气弹簧						建议螺栓 4个	
					GSV	GST	GSH	GSK	GSSC	GSU		
45	35	6.6	9	FCQ	32	350	350	-	150	750	300	CB6-18
52	40	6.6	9		38	500	500	-	250	1000	-	CB6-18
64	50	9	13		45	750	750	-	500	-	-	CB8-25
70	56.5	9	13		50	1000	1000	1000	750	-	-	CB8-25
90	73.5	11	16		63	1500	1500	1500	-	-	-	CB10-35
90	73.5	11	16		75	2400	2400	2400	1500	-	-	CB10-35
110	92	13.5	18		95	4200	4200	4200	3000	-	-	CB12-40
130	109.5	13.5	21		120	6600	6600	6600	5000	12000	-	CB12-40
162	138	17.5	27		150	9500	12000	9500	-	-	18500	CB16-55
210	170	17.5	27		195	20000	-	-	10000	-	-	CB16-55

FCQ符合ISO 11901-2标准。(※FCQ32・63除外)

A	a	d	g	Catalog No.	适用氮气弹簧						建议螺栓 4个	
					GSV	GST	GSH	GSK	GSSC	GSU		
70	56.5	9	13	FCQB	50	-	-	-	-	1800	-	CB8-25
90	73.5	11	16		63	-	-	-	-	3000	-	CB10-35
90	73.5	11	16		75	-	-	-	-	4700	-	CB10-35
110	92	13.5	18		95	-	-	-	-	7500	-	CB12-40

■上槽固定型板可以承受负载。
 但是，请以整个安装面承受负载。



Order
订货范例

Catalog No.

FCC12
FC38
FCB63
FCQ50
FCQB63



Delivery
交货期

请通过 **MISUMI** 询价。
 (https://www.misumi.com.cn)